

Product datasheet

Specifications



SmartX Controller, I/O Module, 8 Form C Relay Digital Outputs

SXWDOC8XX10001

EAN Code: 3606480610523

Main

Flame retardance	UL94V0-5VB
Width	30 mm
Product certifications	ICES-003 FCC part 15 class B CE RCM
Power consumption in VA	2.2 W
Net weight	209 g
Product or component type	I/O module
Device short name	DO-FC-8
Height	114 mm
Ambient air temperature for storage	-20...70 °C
Depth	64 mm
Ambient air temperature for operation	0...50 °C
IP degree of protection	IP20
Relative humidity	0...95 % non-condensing
Product name	I/O Modules
Product brand	Schneider Electric
Range	EcoStruxure Building Operation

Complementary

Discrete output number	8
Mounting support	Wall DIN rail
Electrical connection	Plug-in sub-base
control type	Without
Discrete input voltage	24 V
Discrete output type	Relay
Local signalling	LED (green) for relay energised
Range compatibility	EcoStruxure Building Operation TB-IO-W1 terminal base
Standards	UL 864 UL 916 FCC CFR 47 part 15
Material	ABS + PC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.800 cm
Package 1 Width	9.000 cm
Package 1 Length	12.000 cm
Package 1 Weight	225.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	18
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.505 kg

Logistical informations

Country of origin	SE
-------------------	----

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	88
----------------------------------	----

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	08bd611f-8419-43db-ad4e-34d847346717
REACH Regulation	REACH Declaration
Halogen-free status	Halogen free plastic parts & cables product
PVC free	Yes

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins