

**Productname :** Crick 120  
**Ref.Nr.:** BDS001558\_3\_20140429 (EN)

**Creationdate :** 29.04.14 Version : 1.0  
**Replaces:**

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

**Crick 120**  
 Aerosol

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Welding Products

### 1.3. Details of the supplier of the safety data sheet

**CRC Industries Europe bvba**  
 Touwslagerstraat 1  
 9240 Zele  
 Belgium  
 Tel.: +32(0)52/45.60.11  
 Fax.: +32(0)52/45.00.34  
 E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Laurinkatu 57 A 23 B, 08100 Lohja	+358/(19)32.921	
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303.0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Kryptogatan 14, 431 53 Mölndal	0046/31 706 84 80	0046/31 27 39 91

### 1.4. Emergency telephone number

**CRC Industries Europe, Belgium:** Tel.: +32(0)52/45.60.11 (office hours)

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

#### Classification according to Regulation (EC) No 1272/2008

**Physical:** Aerosols, category 1  
 Extremely flammable aerosol.  
 Pressurised container: May burst if heated.

**Health:** Eye irritation, category 2



**Productname :** Crick 120      **Creationdate :** 29.04.14 Version : 1.0  
**Ref.Nr.:** BDS001558\_3\_20140429 (EN)      **Replaces:**

<b>Environment:</b>	Causes serious eye irritation. Hazardous to the aquatic environment, chronic category 3 Harmful to aquatic life with long lasting effects.
<b>Other hazards :</b>	Repeated exposure may cause skin dryness or cracking. Contains: N-(2-ethylhexyl)-1-[[3-methyl-4-[(3 methylphenyl)azo]phenyl]azo] naphthalen-2-amine May produce an allergic reaction.

### Classification according to 67/548/EEC or 1999/45/EC:

EXTREMELY FLAMMABLE

<b>Health:</b>	R66: Repeated exposure may cause skin dryness or cracking.
<b>Physical:</b>	EXTREMELY FLAMMABLE
<b>Environment:</b>	R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

### 2.2. Label elements

#### Labelling according to Regulation (EC) No 1272/2008

**Hazard pictogram(s):**



<b>Signal word:</b>	Danger
<b>Hazard statement(s):</b>	H222 : Extremely flammable aerosol. H229 : Pressurised container: May burst if heated. H319 : Causes serious eye irritation. H412 : Harmful to aquatic life with long lasting effects.
<b>Precautionary statement(s):</b>	P102 : Keep out of reach of children. P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 : Do not spray on an open flame or other ignition source. P251 : Do not pierce or burn, even after use. P280 : Wear protective gloves/protective clothing/eye protection/face protection. P305/351/338 : IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. P501-2 : Dispose of contents/container to an authorised waste collection point.
<b>Supplemental Hazard information:</b>	Repeated exposure may cause skin dryness or cracking. Contains: N-(2-ethylhexyl)-1-[[3-methyl-4-[(3 methylphenyl)azo]phenyl]azo] naphthalen-2-amine May produce an allergic reaction.

### 2.3. Other hazards

None



**CRC Industries Europe bvba**

Touwslagerstraat 1, 9240 Zele – Belgium

Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

2 / 10

**Productname :** Crick 120  
**Ref.Nr.:** BDS001558\_3\_20140429 (EN)

**Creationdate :** 29.04.14 Version : 1.0  
**Replaces:**

### SECTION 3: Composition/information on ingredients

#### 3.1. Substances

Not applicable.

#### 3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	68512-91-4	270-990-9	50-75	F+	12	K,G
Distillates (petroleum), hydrotreated light; Kerosine - unspecified	64742-47-8	(926-141-6)	25-50	Xn	65-66	B
Solvent naphtha (petroleum), heavy arom. (benzene<0.1%)	64742-94-5	265-198-5	1-5	Xn,N	51/53-65-66-67	B
alcohols, C9-11, ethoxylated	68439-46-3		<3	Xn	22-41	
N-(2-ethylhexyl)-1-[[3-methyl-4-[(3 methylphenyl)azo]phenyl]azo] naphthalen-2-amine	56358-10-2	260-125-3	<1	Xi	38-43	
naphthalene	91-20-3	202-049-5	<0.1	Xn,N	22-40-50/53	A

**Explanation notes**

A : substance with Community workplace exposure limit  
B : substance with national established workplace exposure limit  
G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006  
K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	-	68512-91-4	270-990-9	50-75	Press. Gas, Flam. Gas 1	H280,H220	K,G
Distillates (petroleum), hydrotreated light; Kerosine - unspecified	01-2119456620-43	64742-47-8	(926-141-6)	25-50	Asp. Tox. 1	H304	B
Solvent naphtha (petroleum), heavy arom. (benzene<0.1%)		64742-94-5	265-198-5	1-5	STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2	H336,H304,H411	B
alcohols, C9-11, ethoxylated		68439-46-3		<3	Acute Tox. 4, Eye Dam. 1	H302,H318	
N-(2-ethylhexyl)-1-[[3-methyl-4-[(3 methylphenyl)azo]phenyl]azo] naphthalen-2-amine		56358-10-2	260-125-3	<1	Skin Irrit. 2, Skin Sens. 1	H315,H319	
naphthalene	ABNA	91-20-3	202-049-5	<0.1	Carc. 2, Acute Tox. 4, Aquatic Acute 1, Aquatic Chronic 1	H351,H302,H400,H410	A

**Explanation notes**

A : substance with Community workplace exposure limit  
B : substance with national established workplace exposure limit  
G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006  
K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

(\* Explanation phrases : see chapter 16)



**Productname :** Crick 120  
**Ref.Nr.:** BDS001558\_3\_20140429 (EN)

**Creationdate :** 29.04.14 Version : 1.0  
**Replaces:**

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

<b>Contact with eyes :</b>	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
<b>Contact with skin :</b>	Take off contaminated clothing and wash before reuse. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
<b>Inhalation :</b>	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
<b>Ingestion :</b>	If swallowed accidentally, do not induce vomiting and seek medical advice.

### 4.2. Most important symptoms and effects, both acute and delayed

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting
<b>Skin contact :</b>	May cause irritation. Symptoms : redness and pain
<b>Eye contact :</b>	Irritating to eyes Symptoms : redness and pain

### 4.3. Indication of any immediate medical attention and special treatment needed

<b>General Advice :</b>	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

foam, carbon dioxide or dry agent

### 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products  
CO,CO2

### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

## SECTION 6: Accidental release measures



**Productname :** Crick 120  
**Ref.Nr.:** BDS001558\_3\_20140429 (EN)

**Creationdate :** 29.04.14 Version : 1.0  
**Replaces:**

### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.

### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses  
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

### 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material  
Place in appropriate container

### 6.4. Reference to other sections

For further information see section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/.../equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Ensure adequate ventilation  
Avoid contact with skin and eyes.  
Wash thoroughly after use  
Wear protective gloves/protective clothing/eye protection/face protection.  
Eyewash bottles should be available

### 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
Keep out of reach of children.

### 7.3. Specific end use(s)

Welding Products

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters



**Productname :** Crick 120  
**Ref.Nr.:** BDS001558\_3\_20140429 (EN)  
**Creationdate :** 29.04.14 Version : 1.0  
**Replaces:**

**Exposure limits :**

No information available

**8.2. Exposure controls**

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment. Air purifying respirator equipped with organic gas/vapor cartridge (type A or AX)
<b>hands and skin :</b>	Wear suitable protective gloves against chemicals (nitrile)
<b>eyes :</b>	Wear safety goggles.
<b>Environmental protection:</b>	Avoid release to the environment. Collect spillage.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

(for aerosols data for the product without propellant)

<b>Apperance : physical state :</b>	Propane/butane propelled liquid.
<b>colour :</b>	Red.
<b>odour :</b>	Solvent.
<b>pH :</b>	Not applicable.
<b>Boiling point/range :</b>	Not available.
<b>Flash point :</b>	>62 °C
<b>Evaporation rate :</b>	Not available.
<b>Explosion limits : upper limit :</b>	Not available.
<b>lower limit :</b>	Not available.
<b>Vapour pressure :</b>	Not available.
<b>Relative density :</b>	0.826 g/cm <sup>3</sup> (@ 20°C).
<b>Solubility in water :</b>	Emulsifies with water
<b>Auto-ignition :</b>	> 200 °C
<b>Viscosity :</b>	Not available.

**9.2. Other information****SECTION 10: Stability and reactivity****10.1. Reactivity**

No hazardous reactions known if used for its intended purpose



**Productname :** Crick 120  
**Ref.Nr.:** BDS001558\_3\_20140429 (EN)

**Creationdate :** 29.04.14 Version : 1.0  
**Replaces:**

## 10.2. Chemical stability

Stable

## 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

## 10.4. Conditions to avoid

Avoid overheating

## 10.5. Incompatible materials

Strong oxidising agent

## 10.6. Hazardous decomposition products

CO,CO2

# SECTION 11: Toxicological information

## 11.1. Information on toxicological effects

<b>Inhalation :</b>	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	May cause gastrointestinal disturbances
<b>Skin contact :</b>	May cause irritation.
<b>Eye contact :</b>	Irritating to eyes

### Toxicological data :

Hazardous ingredient	CAS-nr.	method	
N-(2-ethylhexyl)-1-[[3-methyl-4-[(3-methylphenyl)azo]phenyl]azo] naphthalen-2-amine	56358-10-2	LD50 oral rat	> 2000 mg/kg
alcohols, C9-11, ethoxylated	68439-46-3	LD50 oral rat	1000-1400 mg/kg
		LD50 derm.rabit	>2000 mg/kg
Distillates (petroleum), hydrotreated light; Kerosine - unspecified	64742-47-8	LD50 oral rat	> 5000 mg/kg
		LD50 derm.rabit	> 5000 mg/kg

# SECTION 12: Ecological information

## 12.1. Toxicity

Hazardous to the aquatic environment, chronic category 3  
 Harmful to aquatic life with long lasting effects.



**Productname :** Crick 120  
**Ref.Nr.:** BDS001558\_3\_20140429 (EN)

**Creationdate :** 29.04.14 Version : 1.0  
**Replaces:**

**Ecotoxicological data:**

Hazardous ingredient	CAS-nr.	method	
alcohols, C9-11, ethoxylated	68439-46-3	LC50 fish	10-100 mg/l
		EC50 daphnia	5-25 mg/l
Distillates (petroleum), hydrotreated light; Kerosine - unspecified	64742-47-8	IC50 algae	1000 mg/l
		LC50 fish	1000 mg/l
		EC50 daphnia	1000 mg/l

**12.2. Persistence and degradability**

No experimental data available

**12.3. Bioaccumulative potential**

No experimental data available

**12.4. Mobility in soil**

Insoluble in water

**12.5. Results of PBT and vPvB assessment**

No information available

**12.6. Other adverse effects****SECTION 13: Disposal considerations****13.1. Waste treatment methods**

**Product :** This material and its container must be disposed of in a safe way. Do not discharge into drains or the environment, dispose to an authorised waste collection point.  
**National regulations :** Disposal should be in accordance with local, state or national legislation

**SECTION 14: Transport information****14.1. UN number**

UN-number : 1950

**14.2. UN proper shipping name**

Proper shipping name: AEROSOLS



Productname : Crick 120  
Ref.Nr.: BDS001558\_3\_20140429 (EN)

Creationdate : 29.04.14 Version : 1.0  
Replaces:

#### 14.3. Transport hazard class(es)

Class: 2.1  
ADR/RID - Classification code: 5F

#### 14.4. Packing group

Packing group: Not applicable.

#### 14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No  
IMDG - Marine pollutant: No  
IATA/ICAO - Environmentally hazardous: No

#### 14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)  
IMDG - Ems: F-D, S-U  
IATA/ICAO - PAX: 203  
IATA/ICAO - CAO: 203

#### 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.  
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.  
EU-directive 99/45/EC  
Regulation (EC) No 1272/2008 (CLP)  
Regulation (EC) No 1907/2006 (REACH)

#### 15.2. Chemical safety assessment

No information available

### SECTION 16: Other information

\*Explanation risk-phrases: R12: Extremely flammable.  
R22: Harmful if swallowed.  
R38: Irritating to skin.  
R40: Limited evidence of a carcinogenic effect.  
R41: Risk of serious damage to eyes.



---

<b>Productname :</b>	Crick 120	<b>Creationdate :</b>	29.04.14 Version : 1.0
<b>Ref.Nr.:</b>	BDS001558_3_20140429 (EN)	<b>Replaces:</b>	

---

R43: May cause sensitization by skin contact.  
R65: Harmful: may cause lung damage if swallowed.  
R66: Repeated exposure may cause skin dryness or cracking.  
R67: Vapours may cause drowsiness and dizziness.  
R50/53: Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.  
R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

\*Explanation hazard statements: H220 : Extremely flammable gas.  
H280 : Contains gas under pressure; may explode if heated.  
H302 : Harmful if swallowed.  
H304 : May be fatal if swallowed and enters airways.  
H315 : Causes skin irritation.  
H318 : Causes serious eye damage.  
H319 : Causes serious eye irritation.  
H336 : May cause drowsiness or dizziness.  
H351 : Suspected of causing cancer .  
H400 : Very toxic to aquatic life.  
H410 : Very toxic to aquatic life with long lasting effects.  
H411 : Toxic to aquatic life with long lasting effects.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.