

# KSA1000DMCK41F

Multiple, Canalis KSA1000, aluminium, 800/1000A, side B made to measure, fire barrier, downward then turns left, RAL9001

## Main

Range of product	Canalis
Product name	KS
Device short name	KSA
Offer type	Advanced
Product or component type	Multiple elbow
Busbar description	Fire barrier on made to measure (only one side)
Product compatibility	Canalis KSA busbar trunking 500...1000 A
Device application	Change direction
Conductors material	Aluminium
Busbar trunking polarity	3L + N + PE
[Ie] rated operational current	1000 A at 35 °C
IP degree of protection	IP55 conforming to IEC 60529
[Ue] rated operational voltage	230...690 V
Network frequency	50/60 Hz
Operating angle	90 °
Direction change type	Direction 1: edgewise to downward - Direction 2: flat to left -
Colour	White (RAL 9001)
Dimension type	Made to measure
Length	290 Mm for side A 700...1200 Mm for side B 290 mm for side C




## Complementary


Width	113 mm
Depth	146 mm
Mounting location	On trunking
Mounting mode	By screws
Electrical connection	Lubricated sliding contact
Standards	IEC 61439-1 IEC 61439-6

## Environment

IK degree of protection	IK08 conforming to IEC 62262
-------------------------	------------------------------

## Offer Sustainability

Packaging without single use plastic	Yes
Packaging made with recycled cardboard	No
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	No