

MC122032B6W-SPTLY-V2	122 x 32		LCD Module
<b>Specification</b>			
Version: 1		Date: 31/10/2016	
<b>Revision</b>			

Display Features							
Resolution	122 x 32						
Appearance	Black on Yellow/Green						
Logic Voltage	5V						
Interface	Parallel						
Font Set	N/A						
Display Mode	Transflective						
LC Type	STN						
Module Size	84.00 x 44.00 x 15.00						
Operating Temperature	-20°C ~ +70°C						
Construction	COB					Box Quantity	Weight / Display
LED Backlight	Yellow/Green					45 pcs	28.88 grams

\* - For full design functionality, please use this specification in conjunction with the SBN1661G\_M02 specification.(Provided Separately)


Display Accessories	
Part Number	Description
VBWFD1	USB PIC18F2550 microcontroller board to 20-way Single in-line COB Graphic LCD.

Optional Variants	
Appearances	Voltage
Black on White White on Blue	



## Mechanical Specifications

Module Size	84.00 x 44.00 x 15.00 ( With Backlight)				W x H x D mm
Viewing Area	64.00 x 17.90	W x H mm	Hole-to-Hole	76.00 x 36.00	W x H mm
Dot Size	0.40 x 0.45	W x H mm	Dot Pitch	0.04 x 0.04	W x H mm



MC122032B6W-SPTLY-V2	122 x 32	<b>Specification</b>	LCD Module
Version: 1	Date: 31/10/2016		
<b>Revision</b>			




# Pin Layout


Dj <b>b</b>	Gra Vc`	8 YgWjdHjcb	FYa Uf_g
1	Vss	GND	
2	Vdd	Power Supply for LCM	5.0V
3	V0	Contrast Adjust	
4	A0	H/L H: Data; L: Instruction Code	
5	CS1	Chip 1 Enable Signal	
6	CS2	Chip 2 Enable Signal	
7	CL	Clock Input (2 KHz)	
8	E	Enable Signal	
9	R/W	Data Read / Write	
10	DB0	Data bus Line	
11	DB1	Data bus Line	
12	DB2	Data bus Line	
13	DB3	Data bus Line	
14	DB4	Data bus Line	
15	DB5	Data bus Line	
16	DB6	Data bus Line	
17	DB7	Data bus Line	
18	RST	Reset Signal	
19	LED+	Power Supply for BKL	5.0V
20	LED-	Power Supply for BKL	

MIDAS  
DISPLAYS

## Block Diagram



## Power Supply Diagram



MC122032B6W-SPTLY-V2	122 x 32	LCD Module
<b>Specification</b>		
Version: 1	Date: 31/10/2016	
<b>Revision</b>		



### Absolute Maximum Ratings

Item	Symbol	Condition	Min	Typ	Max	Unit
Power Supply ( LOGIC)	Vdd	25°C	-0.3	---	7.0	V
Power Supply (LCD)	V0	25°C	Vdd -19.00	---	Vdd +0.3	V
Input Voltage	Vin	25°C	-0.3	---	Vdd +0.3	V
Operating Temperature	Vopr	---	-20	---	70	C
Storage Temperature	Vstg	---	-30	---	80	C

### Electronic Characteristics

Item	Symbol	Condition	Min	Typ	Max	Unit
Input Voltage	Vlcm = Vdd	---	---	5.0	---	V
Supply Current	Idd	Vdd=5V	---	1.50	---	mA
Driving Voltage for LCD Panel	Vlcd = (Vdd - V0)	-20°C	3.90	---	4.20	V
		0°C	3.95	---	4.25	
		25°C	4.00	---	4.40	
		50°C	4.05	---	4.45	
		70°C	4.10	---	4.50	

### LCD Characteristics

For STN/FSTN LCD Panel Types						
Item	Symbol	Condition	Min	Typ	Max	Unit
Viewing Angle	$\Phi 2 - \Phi 1$	K = 4	40°	---	---	Deg
	$\Theta$		60°			
Contrast Ratio	K	---	---	10	---	---
Response Time (Rise)	TR	---	---	150	250	ms
Response Time (Fall)	TF	---	---	150	250	ms

### LED Characteristics

Item	Symbol	Condition	Min	Typ	Max	Unit
LED Forward Voltage	Vf	25°C I <sub>f</sub> = 5mA	2.8	---	3.1	V
LED Forward Current*	I <sub>f</sub>	25°C	---	5	---	mA
LED Reverse Current	I <sub>r</sub>	25°C V <sub>r</sub> =5.0V	---	---	10	μA
LED Peak Wave Length	λ <sub>p</sub>	25°C I <sub>f</sub> = 5mA	569	---	575	nm
LED Brightness (Without LCD)	L <sub>v</sub>	25°C I <sub>f</sub> = 5mA	---	85	---	cd/m <sup>2</sup>
LED Brightness Uniformity	L <sub>vmin</sub> /L <sub>vmax</sub>	25°C I <sub>f</sub> = 5mA	70	---	---	Ratio
LED Life Time		25°C I <sub>f</sub> = 5mA	20K	---	---	Hours

**Attention:** It is constant current, not constant voltage, which should be applied when driving the LED backlight, please ensure you adhere to this rule.

MC122032B6W-SPTLY-V2	122 x 32		LCD Module
<b>Specification</b>			
Version: 1		Date: 31/10/2016	
<b>Revision</b>			
			Page 4 of 4