



[ 2 YEAR WARRANTY ]

 (LVD & EMC)

## SCL25 SERIES

Single, dual and triple output

- **6.32 x 3.35 x 1.5 inch enclosure**
- **25W external power supply**
- **Molded UL94V-0 plastic enclosure**
- **Output connector options**
- **Stand alone 'listed' equipment**
- **Short circuit protection**
- **EN55022, EN55011 conducted emissions level B**
- **UL, CSA and VDE safety approvals**

The SCL25 series is a 25W universal input AC/DC external power supply in a 6.32 x 3.35 x 1.5 inch plastic enclosure. The SCL25 series has seven single output and three multiple output models in a low profile package providing a pre-approved external power solution for a host of worldwide low power portable and desktop applications. The SCL25 provides 25W of output power with free air convection cooling which can peak at 30W for 60 seconds. Standard features include universal input, short circuit protection and EN55022 conducted emissions level B. The series, with full international safety approval and the CE mark, provides pre-approved SELV outputs without the need for further safety approval or mechanical integration into the application system. The SCL25 series is designed for use in low power, and desktop data networking, computer and industrial applications requiring external power adapters in a low profile package.

## SPECIFICATION

All specifications are typical at nominal input, full load at 25°C unless otherwise stated

OUTPUT SPECIFICATIONS		
Line regulation LL to HL, FL	Single outputs Multi's: +5V output Multi's: aux. outputs	±0.5% ±0.5% ±1.0%
Total regulation NL to FL (See Note 5)	Single outputs Multi's: +5V output Multi's: aux. outputs	±4.0% +6.0%/-4.0% see table
Overshoot/Uundershoot	At turn on	10%
Transient response	+5V output (40% FL to 60% full load step)	±250mV max. dev., 1ms recovery to 1.0%
Temperature coefficient		±0.02%/ <sup>o</sup> C, max.
Overvoltage protection	+5V Output, Note 9	6.25V ±0.65V
Output power limit	Primary power limited	80W Pin max. 40W Pout min.
Short circuit protection		Continuous with auto-restart
Green LED indicator	See Note 7	Normally ON
INPUT SPECIFICATIONS		
Input voltage range		90 to 264VAC
Input frequency range		47Hz to 63Hz
Input surge current		36A max.
Safety ground leakage current	110VAC, 60Hz 230VAC, 50Hz	0.2mA 0.4mA
EMC CHARACTERISTICS		
Radiated noise	EN55022, EN55011, FCC P15	Level B
Conducted noise	EN55022, EN55011, FCC P15	Level B
Electrostatic discharge	EN61000-4-2	Level 4
Electrostat. air discharge	IEC801-2	Level 3
RF field susceptibility	IEC801-3	Level 2
Electrical fast transients/bursts	EN61000-4-4	Level 3
Surge susceptibility	EN61000-4-5	Level 3

GENERAL SPECIFICATIONS		
Hold-up time	110VAC 230VAC	10ms 60ms
Efficiency	110VAC and 230VAC	70% typical
Isolation voltage	Input/output Input/chassis	3000VAC 1500VAC
Switching frequency	Variable	35kHz to 80kHz
Approvals and standards	Safety	VDE0805, EN60950 IEC950, UL1950, BART CSA C22.2 No. 950
Case Material	General Electric Lexan, Black	
Flammability rated	UL94V-0	
Weight	450g (15.9oz)	
MTBF	MIL-HDBK-217F	150,000 hours
ENVIRONMENTAL SPECIFICATIONS		
Thermal performance	Operating, full load, no derating Non-operating	0°C to +40°C -40°C to +85°C
	0°C to +40°C ambient, convection cooled	25W
	Peak (0°C to +40°C, max. 60s)	30W
	See Note 3	
Relative humidity	Non-condensing	5% to 95% RH
Altitude	Operating Non-operating	10,000 feet max. 30,000 feet max.
Vibration	Three orthogonal axes 5Hz to 500Hz	2.4G rms random vibration, 10 minute test for each axis

25 Watt  
AC/DC external power supplies

OUTPUT VOLTAGE	OUTPUT CURRENTS			RIPPLE <sup>(4)</sup>	TOTAL REGULATION <sup>(5)</sup>	MODEL NUMBER	
	MIN <sup>(1)</sup>	MAX <sup>(2)</sup>	PEAK <sup>(3)</sup>				
+5V (1)	0A	2.0A	4.0A	50mV	+6.0%, -4.0%	SCL25-7608	
+12V (2)	0A	1.0A	2.0A	120mV	+7.0%, -5.0%		
-12V (3)	0A	0.2A	1.0A	120mV	±5.0%		
+5V (1)	0A	2.0A	4.0A	50mV	+6.0%, -4.0%	SCL25-7610	
+15V (2)	0A	0.75A	1.5A	150mV	+9.0%, -3.0%		
-15V (3)	0A	0.2A	1.0A	150mV	±5.0%		
+5V (1)	0A	2.5A	4.0A	50mV	+6.0%, -4.0%	SCL25-7618	
+12V (2)	0A	1.0A	2.0A	120mV	+7.0%, -5.0%		
+5V (1)	0A	4.0A	5.0A	50mV	+6.0%, -4.0%	SCL25-7605	
+9.5V (1)	0A	2.5A	3.2A	95mV	±4.0%	SCL25-7614	SCL25-7614H1 <sup>(6)</sup>
+12V (1)	0A	2.0A	2.5A	120mV	±4.0%	SCL25-7612	SCL25-7612H1 <sup>(6)</sup>
+14V (1)	0A	1.7A	2.2A	140mV	±4.0%	SCL25-7621	SCL25-7621H1 <sup>(6)</sup>
+16V (1)	0A	1.5A	2.0A	160mV	±4.0%	SCL25-7616	SCL25-7616H1 <sup>(6)</sup>
+24V (1)	0A	1.0A	1.3A	240mV	±4.0%	SCL25-7624	SCL25-7624H1 <sup>(6.9)</sup>
+48V (1)	0A	0.5A	0.7A	240mV	±4.0%	SCL25-7617	SCL25-7617H1 <sup>(6.9)</sup>

## Notes

- 1 Although the SCL25 models will operate with no load on the outputs, some components temperatures increase under this condition. To maximize reliability, a minimum total load of 4W is recommended.
- 2 Natural convection cooling, 25W maximum.
- 3 Peak output current lasting less than 60 seconds with duty cycle less than 5%. During peak loading, output voltage may exceed total regulation limits.
- 4 50MHz bandwidth, peak to peak, measured differentially.
- 5 Total regulation is defined as the static output regulation at 25°C, including initial tolerance, line voltage within stated limits, load currents within stated

For maximum output current  $I(3)$  on triple-output models, i.e. for  $I(3)=I_{Max}$ , then  $I(1)$  min.  $\geq 0.5A$  and  $I(2) \geq I(3)$ .

- 6 An alternative 48 inch cable assembly with 2.5mm jack plug is available on single output models (except 7605 model). This option can be ordered by adding the suffix 'H1' to the end of the model number, e.g. **SCL25-7614H1**, see table above for availability.
- 7 The green LED is ON to indicate the presence of output (1). The LED turns off during output short circuit condition.
- 8 To maintain user-system safety approvals, the input power cable must be appropriately rated and approved.
- 9 Overvoltage protection is standard on -7617 and -7624 and 5V output (single and multiple output) models.

51.2 REF  
(1300.00±15)

## International Safety Standard Approvals



 VDE0805/EN60950/IEC950 File No. 10401-3336-1083  
Licence No. 1083



UL UL1950 File No. E136005



 CSA C22.2 No. 950 File No. LR41062



CERTIFIED BY Certification pending

PIN CONNECTIONS MINI DIN PLUG				
OUTPUT PIN NO.	SINGLE OUTPUT	DUAL OUTPUT	TRIPLE OUTPUT	MATING CONNECTOR
1	V <sub>A</sub>	V <sub>A</sub>	V <sub>A</sub>	AMP Shielded Miniature circular DIN Plug 8 Pin P/N 749179-1 or equivalent
2	V <sub>A</sub>	V <sub>A</sub>	V <sub>A</sub>	
3	V <sub>A</sub>	V <sub>A</sub>	V <sub>A</sub>	
4	V <sub>A</sub>	V <sub>B</sub>	V <sub>B</sub>	
5	Return	Return	V <sub>C</sub>	
6	Return	Return	Return	
7	Return	Return	Return	
8	Return	Return	Return	
PIN CONNECTIONS 2.5mm Jack Plug				
Inner	V <sub>A</sub>			SWITCHCRAFT Power
Outer	Return			Jack, P/N 712A or Equivalent

