

Product description	<b>M12 Male panel mount connector, Contacts: 4, unshielded, solder, IP67, M12x0.5, transparent housing</b>
Area	<b>M12-A</b>
Coding	<b>A-coded</b>
Series	<b>713</b>
Part no.	<b>09 0431 80 04</b>

## Technical data

### General features

Part no.	<b>09 0431 80 04</b>
Connector design	Male panel mount connector
Type standard	DIN EN 61076-2-101
Coding	A-coded
Connector locking system	screw
Termination	solder
Degree of protection	IP67
Connection cross-section	0.25 mm <sup>2</sup> / AWG 24
Temperature range from/to	-40 °C / 85 °C
Mechanical operation	> 100 Mating cycles
Weight (g)	3.15
Customs tariff number	85369010
Country of Origin	DE

### Electrical parameters

Rated voltage	250 V
Rated impulse voltage	2500 V
Rated current	4.0 A
Pollution degree	3
Overvoltage category	II
Insulating material group	III
EMC compliance	unshielded

### Material

Contact body material	PA
Contact material	CuZn (brass)
Contact plating	Au (gold)
Locking material	PA
REACH SVHC	CAS 7439-92-1 (Lead)
SCIP number	90096df7-7893-4b41-9ffb-38f2b2f376ad

### Classifications

eCl@ss 11.1	27-44-01-09
ETIM 9.0	EC003569

Product description	<b>M12 Male panel mount connector, Contacts: 4, unshielded, solder, IP67, M12x0.5, transparent housing</b>
Area	<b>M12-A</b>
Coding	<b>A-coded</b>
Series	<b>713</b>
Part no.	<b>09 0431 80 04</b>

## General Disclaim Notice

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

Connectors which are used in circuits with voltages dangerous to the touch may only be installed and used by, or under the supervision of, persons with electrical engineering training, taking into account the applicable regulations and standards.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Plug connectors with enclosure protection IP67 and IP68 are not suitable for use under water. When used outdoors, the plug connectors must be protected separately against corrosion. For further information on the IP protection classes, please refer to the "Technical Information" download centre.

Please observe the pollution degree and the overvoltage category. For further information, please refer to the download center "Technical Information".

To lock the cable connector with the device connector, the threaded ring is tightened "hand-tight" (approx. 60 cNm).