


RE、ST Series Control Valve




RE Flow Capacity control Valve



Symbol:



Dimension(mm):



Specification:

Type	RE-06	RE-08	RE-10	RE-15
Port size(G)	G1/8"	G1/4"	G3/8"	G1/2"
Fluid	Compressed air			
Working pressure(MPa)	0.05~0.8			
Ambient temperature(°C)	-5~60			
Material	Aluminum alloy			

How to order:

RE	06
Specification	Port size
RE: Flow Capacity Control Valve	06: G1/8"
	08: G1/4"
	10: G3/8"
	15: G1/2"

Type	A	B	C	D	E	F	W1	W2	W3
RE-06	45	19	46	53	G1/8"	M14×1	11	17	23
RE-08	45	19	46	53	G1/4"	M14×1	11	17	23
RE-10	55	25	52	59	G3/8"	M18×1	11	17	23
RE-15	55	25	52	59	G1/2"	M18×1	11	17	23




ST Shuttle Valve



Dimension(mm):

ST-06, 08



Specification:

Type	ST-06	ST-08
Port size(G)	G1/8"	G1/4"
Fluid	Compressed air	
Operating pressure(Mpa)	0.05~0.8	
Ambient temperature(°C)	-5~60	

How to order:

ST	06
Specification	Port size
ST: Shuttle Valve	06: G1/8"
	08: G1/4"