

Product data sheet

Miniature connectors




Product description	M16 Female panel mount connector, Contacts: 8 (08-a), unshielded, solder, IP40
Area	M16 IP40 series 680
Part no.	09 0474 00 08


Illustration



Scale drawing



Contact arrangement (Plug-in side)



You can find the component part drawing and assembly instructions on the next page.

Technical data

General features

Part no.	09 0474 00 08
Connector design	Female panel mount connector
Type standard	DIN EN 61076-2-106
Version	Connector socket straight
Connector locking system	screw
Termination	solder
Degree of protection	IP40
Cross-sectional area	0.75 mm ² / AWG 18
Temperature range from/to	-40 °C / 85 °C
Mechanical operation	> 500 Mating cycles
Weight (g)	9.16
Customs tariff number	85369010
Country of Origin	DE

Electrical parameters

Rated voltage	60 V
Rated impulse voltage	500 V
Rated current	5.0 A
Insulation resistance	≥ 10 ¹⁰ Ω
Pollution degree	1
Overvoltage category	I
Insulating material group	III
EMC compliance	unshielded

Product data sheet

Miniature connectors



Product description	M16 Female panel mount connector, Contacts: 8 (08-a), unshielded, solder, IP40
-	-
Area	M16 IP40 series 680
Part no.	09 0474 00 08

Material

Housing material	Zinc die-cast nickel-plated
Contact body material	PBT (UL94 V-0)
Contact material	CuSn (bronze)
Contact plating	Ag (silver)
REACH SVHC	CAS 7439-92-1 (Lead)
SCIP number	8aa4c741-fb09-4012-9b72-71a7870676b5

Classifications


eCl@ss 11.1	27-44-01-09
ETIM 9.0	EC003569

Product data sheet
Miniature connectors



Product description	M16 Female panel mount connector, Contacts: 8 (08-a), unshielded, solder, IP40
-	-
Area	M16 IP40 series 680
Part no.	09 0474 00 08

Assembly instructions / Panel cut-out




Product data sheet

Miniature connectors



Product description	M16 Female panel mount connector, Contacts: 8 (08-a), unshielded, solder, IP40
-	-
Area	M16 IP40 series 680
Part no.	09 0474 00 08

Component part drawing



Product description	M16 Female panel mount connector, Contacts: 8 (08-a), unshielded, solder, IP40
-	-
Area	M16 IP40 series 680
Part no.	09 0474 00 08

Security notices

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.