



ELECTRICAL DOUBLE LAYER ENERGY STORAGE CAPACITORS

220 EDLC ENYCAP™

Electrical Double Layer Energy Storage Capacitors Power and Energy Versions



KEY BENEFITS

- Polarized energy storage capacitor with high capacity and high energy density
- Rated voltage: 2.7 V
- Rapid charge and discharge
- Available in through-hole (radial) version
- Non-hazardous electrolyte
- RoHS-compliant

APPLICATIONS

- Power backup
- Burst power support
- Storage device for energy harvesting
- Micro UPS power source
- Energy recovery

RESOURCES

- Datasheet: 220 EDLC - <http://www.vishay.com/doc?28421>
- For technical questions contact hybridstorage@vishay.com
- Material categorization: For definitions of compliance please see <http://www.vishay.com/doc?99912>



RoHS
COMPLIANT

A WORLD OF
SOLUTIONS

Electrical Double Layer Energy Storage Capacitors Power and Energy Versions




Image is not to scale

QUICK REFERENCE DATA	
DESCRIPTION	VALUE
Nominal case sizes (∅ D x L in mm)	16 x 20; 18 x 20; 16 x 31; 18 x 31
Rated capacitance range, C _R	15 F to 40 F
Rated voltage, U _R (65 °C / 85 °C)	2.7 V / 2.3 V
Category temperature range	-40 °C to +85 °C
Endurance test at 85 °C	1000 h
Useful life at 85 °C	1000 h
Useful life at 20 °C	> 10 years
Shelf life at 20 °C	2 years
Cycle life	> 500 000 cycles

FEATURES

- Polarized energy storage capacitor with high capacity and energy density
- Energy version with high stability available
- Rated voltage: 2.7 V
- Available in through-hole (radial) version
- Useful life: 1000 h at 85 °C
- Rapid charge and discharge
- Maintenance-free, no service necessary
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

APPLICATIONS

- Power backup
- Burst power support
- Storage device for energy harvesting
- Micro UPS power source
- Energy recovery

MARKING

The capacitors are marked (where possible) with the following information:

- Rated capacitance (in F)
- Tolerance on rated capacitance, code letter in accordance with IEC 60062 (A)
- Rated voltage (in V)
- Date code, in accordance with IEC 60062
- Code indicating factory of origin
- Logo of manufacturer
- Negative terminal identification
- Series number (220)

PACKAGING

Supplied in ESD trays.

SELECTION CHART FOR C_R, U_R, AND RELEVANT NOMINAL CASE SIZES (∅ D x L in mm)

C _R (F)	U _R (V) = 2.7 V
15	16 x 20
20	16 x 20; 18 x 20
25	18 x 20
30	16 x 31
35	16 x 31, 18 x 31 ⁽¹⁾
40	18 x 31 ⁽¹⁾

Note

⁽¹⁾ Preferred case size.

Revision 05-Nov-15