

FEATURES

- Button head hexagonal socket screws to DIN7380 standards
- A2 stainless steel
- Generally non-magnetic
- Cannot be hardened by heat treatment
- Supplied in a polypropylene case

490 piece Stainless Steel Screw/Bolt Kit, M3, M4, M5, M6

RS Stock No.: 393-169



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted RS PRO brand, this set of high-quality button head hexagonal socket screws have a cylindrical head and an internal hex drive. Socket screws are tightened using an Allen or Hex key, making them ideal for use in applications where externally wrenched fasteners are not practical because of a lack of space. Button-headed screws have a larger head diameter than the screw shaft, making them more appropriate for holding thin materials such as sheet metal guards.

General Specifications


Number Of Pieces	490
Screw/Bolt Type	Socket Screw
Head Shape	Button
Drive Type	Hex Socket
Kit Contents	M3 x 8 Qty-100; M3 x 10 Qty-50; M4 x 8 Qty-50; M4 x 10 Qty-50; M4 x 12 Qty-50; M4 x 16 Qty-50; M5 x 10 Qty-40; M5 x 12 Qty-30; M5 x 16 Qty-20; M6 x 12 Qty-20; M6 x 16 Qty-15; M6 x 20 Qty-15;
Applications	Carpentry, Construction, DIY applications, such as cabinets and paneling

Mechanical Specifications

Screw/Bolts Lengths	8mm to 20mm
Thread Size	M3, M4, M5, M6
Material	Stainless Steel
Stainless Steel Type	A2 304
Finish	Plain
Screw/Bolt Length Longest	20mm
Screw/Bolt Length Shortest	8mm



393-169



M3 x 8 RS 183-8597	M4 x 8 RS 183-8626	M3 x 10 RS 183-8604	M4 x 12 RS 183-8648
M5 x 12 RS 183-8676	M4 x 10 RS 183-8632	M5 x 10 RS 183-8660	M4 x 16 RS 183-8654
M6 x 16 RS 183-8727	M6 x 20 RS 183-8733	M6 x 12 RS 183-8711	M5 x 16 RS 183-8698

Kit Contents			
Size	Quantity	Size	Quantity
M3 x 8	100	M5 x 10	40
M3 x 10	50	M5 x 12	30
M4 x 8	50	M5 x 16	20
M4 x 10	50	M6 x 12	20
M4 x 12	50	M6 x 16	15
M4 x 16	50	M6 x 20	15