




Brand of NTN corporation



Technical data

5213EEG15

Double row angular contact ball bearings



VISUAL (S)



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

Brand	SNR
d - Internal diameter	65 mm
D - External diameter	120 mm
B - Bearing/Inner ring width	38,1 mm
d1 - External diameter inner ring	82 mm
D1 - Inner diameter outer ring	106,9 mm
a - Charge load application point	59,8 mm
- Contact angle	25 °
rs - Min fillet radius	1,5 mm
Radial clearance class	CN
Precision class	P0
Mass	1,52 kg

PRODUCT PERFORMANCE

C - Dynamic load	74100000 mN
C0 - Static load	70600000 mN
Cu - Fatigue limit load	4200000 mN
f0 - Coefficient	14.7
N lim - Mechanical Limit Speed	21000 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

BEARING FREQUENCIES

BPFO - Over rolling frequency on outer ring (60 rpm)	4.678 Hz
BPFI - Over rolling frequency on inner (60 rpm)	6.322 Hz



5213EEG15

Double row angular contact ball bearings

BEARING FREQUENCIES

BSF - Over rolling frequency on rolling element (60 rpm)	5.929 Hz
BRF - Rotational frequency - rolling element (60 rpm)	2.965 Hz
FTF - Rotational frequency - cage (60 rpm)	0.425 Hz

ABUTMENT

da min - Min shoulder diameter IR	73 mm
da max - Max shoulder diameter IR	82 mm
Da max - Max shoulder diameter OR	112 mm
ra max - Max shaft & housing fillet radius	1,5 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15