



Main

| | |
|---------------------------|--------------------------------------|
| Range of product | Harmony XB5 |
| Product or component type | Wireless and batteryless transmitter |
| Device short name | XB5R |
| Bezel material | Chromium plated metal |
| Fixing collar material | Zamak |
| Mounting diameter | 22 mm |

Complementary


| | |
|------------------------------|---------------|
| Shape of signaling unit head | Round |
| Type of operator | Spring return |
| Operator profile | 1 flush green |
| Embedding depth | <= 42 mm |
| CAD overall height | 41.5 mm |
| CAD overall width | 30 mm |
| CAD overall depth | 43 mm |
| Product weight | 0.045 kg |

Environment

| | |
|---------------------------------------|--|
| Protective treatment | TH |
| Ambient air temperature for storage | -40...70 °C |
| Ambient air temperature for operation | -25...55 °C |
| IP degree of protection | IP65 on front face conforming to IEC 60529 IP30 on back face conforming to IEC 60529 |
| IK degree of protection | IK03 conforming to IEC 50102 |
| Mechanical durability | 1000000 cycles |
| Vibration resistance | 5 gn (f= 11...500 Hz) conforming to IEC 60068-2-6 |
| Shock resistance | 30 gn (duration = 18 ms half sine wave acceleration) conforming to IEC 60068-2-27 50 gn (duration = 11 ms half sine wave acceleration) conforming to IEC 60068-2-27 |
| Standards | CSA C22-2 No 14 EN/IEC 60947-5-1 UL 508 EN 300-440-1 EN 300-440-2 EN 301-489-1 EN 301-489-3 |
| Product certifications | CE C-Tick FCC GOST ANATEL SRRC BT 2006/95/EC EMC directive 2004/108/EC R&TTE directive 1999/5/EC RSS |

Wireless and Batteryless Pushbutton - Transmitter

With Metal Pushbutton and Cap



e: panel thickness 1 to 6 mm / 0.039 to 0.24 in.