



PLASTI-GRIP

TE Internal #: 8-321026-1

Yellow, Butt Splice, 26 – 22 AWG, .12 – .4 mm² Wire, 202 – 810
 CMA, Fully Insulated, Serrated, Copper, 15.75 mm [.62 in] Length,
 PLASTI-GRIP

[View on TE.com >](#)

Terminals & Splices > Splices



Splice Type: **Butt Splice**

Wire Size: .12 – .4 mm²

Sealable: **No**

Splice Features: **Serrated**

Features

Product Type Features

Splice Accessory Type	Splice
Splice Type	Butt Splice
Sealable	No
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Product Weight	.257 g
Insulation Material	Vinyl
Splice Features	Serrated
Primary Product Color	Yellow

Contact Features

Terminal Plating Material	Tin
---------------------------	-----



Contact Base Material	Copper
-----------------------	--------

Barrel Type	Closed
-------------	--------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	202 – 810 CMA
-----------	---------------

Compatible Insulation Diameter Range	2.03 mm[.08 in]
--------------------------------------	-----------------

Product Length	15.75 mm[.62 in]
----------------	------------------

Usage Conditions

Insulation Option	Fully Insulated
-------------------	-----------------

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	100
--------------------	-----

Packaging Method	Loose Piece
------------------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
--	---

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as

EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | PLASTI-GRIP




Compression Connectors(3)



Crimp Wire Pins, Tabs & Ferrules(20)



Ring Terminals(310)



Spade Terminals(158)



Splices(45)

Customers Also Bought



TE Part #CSI-RGFB-100-UFFR
RP-SMA to U.FL/MHF1 100mm 1.13
OD



TE Part #CSE-SGAM-610-SGFB
SMA to SMA 610mm RG316



TE Part #53942-2
TERMINAL, PIDG R 16-14 10



TE Part #5-747912-4
25 PLUG SOLDER CUP STD DUPL, R



TE Part #1393194-9
T77S1D10-12



TE Part #2-1419104-1
T9AS1D22-24



TE Part #1586958-1
03P UMNL PIN HDR ASSY NATL, GW



TE Part #5-1618388-8
LEV200A6NAA=RELAY, SPST-NO



TE Part #2-1630012-8
HSC150 22R 5%



TE Part #3-1879022-7
SMF3 10K 5%

Documents

Product Drawings

[SPLICE,PG BUTT 26-22](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_8-321026-1_G.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_8-321026-1_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_8-321026-1_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

8-321026-1

Yellow, Butt Splice, 26 – 22 AWG, .12 – .4 mm² Wire, 202 – 810 CMA, Fully Insulated, Serrated, Copper, 15.75 mm [.62 in] Length, PLASTI-GRIP



Application Specification

English