


FEATURES

- **High-quality materials:** Provides excellent chemical resistance and durability
- **Wide temperature range:** Operates effectively from -20 °C to 140 °C
- **Precise dimensions:** Inside diameter of 101.27 mm and outside diameter of 106.51 mm for a secure fit
- **Compliance with standards:** Meets BS ISO 3601-1, AS 568, EC 1935:2004, and more for assured quality
- **Shore A hardness of 90 to 95:** Ensures a robust and reliable seal

RS PRO 101.27 mm O-Ring Seal, Shore A 90 to 95

RS Stock No: 731-594



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO O-Ring Seal is designed for reliable sealing in a variety of industrial applications. Made from high-quality materials such as Fluorinated Ethylene Propylene, Fluoroelastomer, and Viton, it offers excellent chemical resistance and durability. With a hardness of Shore A 90 to 95, it ensures a secure fit and optimal performance in demanding environments.

General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

Mechanical Specifications

Inside Diameter	101.27 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	106.51 mm
Thickness	2.62 mm

Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

