



 
SADDLE CLAMP & SCREW
(FURNISHED IN BULK)

DWG NO. TIGK57-6S-BL-NBL		REV.
LET	REVISIONS	DATE

RATING: UL, CSA

10AMP 250VAC
15AMP 125VAC
3/4HP 125 - 250VAC

OPERATES:

POSITIONS OF TIPPER

POS 1	POS 2	POS 3
ON	NONE	OFF
T2 TO 3		
T5 TO 6		

NOTES:

1. SNAP-IN BRACKET IS BLACK, ROCKER IS BLACK NYLON
3. BRACKET SNAPS INTO PANEL THICKNESS , .040 - .250
4. .250 TAB / COMBI TERMINALS AT T2, 3, 5, & 6

DIMENSIONS SUBJECT TO CHANGE WITHOUT NOTICE

FINISH _____	
TOOL NO. _____	
DR BY KRAMARZ	DATE 7-14-11
CHK BY	DATE
APPD BY	DATE

CARLINGSWITCH, INC.
PLAINVILLE, CT

PROPRIETARY NOTE:

NOTICE TO ALL PERSONS RECEIVING THIS DRAWING. THIS DOCUMENT IS THE PROPERTY OF CARLINGSWITCH, INC. AND IS NOT TO BE DISCLOSED, REPRODUCED IN WHOLE OR IN PART OR USED FOR MANUFACTURING PURPOSES BY ANYONE WITHOUT THE CONSENT OF CARLINGSWITCH, INC.

UNSPECIFIED TOLERANCES

FRAC. $\pm 1/64$ X.XXX $\pm .015$
ANGLES $\pm 1^\circ$

PROJECTIONS 	DIMENSIONS IN [mm]
--	-----------------------

TITLE
TIPPETTE SWITCH

SIZE A	DWG NO. TIGK57-6S-BL-NBL	REV. _____
USED ON _____	SCALE: NONE	SHT OF 1 1