




Connectors > PCB Connectors > Card Edge Connectors > PCI & PCI Express Connectors



Connector System: **Board-to-Board**

Number of Positions: **36**

PCI Generation: **2 & 3**

Centerline (Pitch): **1 mm [.039 in]**

Termination Post & Tail Length: **3.93 mm [.16 in]**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board

Configuration Features

Number of Positions	36
PCB Mount Orientation	Straddle Mount
Ejector	Without

Electrical Characteristics

Operating Voltage	50 VAC
-------------------	--------

Body Features

Product Weight	2.9 g[.102 oz]
Primary Product Color	Black

Contact Features

Contact Current Rating (Max)	1.1 A
PCB Contact Termination Area Plating Material Thickness	2.54 μm
Contact Mating Area Plating Material	Gold (Au)



Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin
PCB Contact Termination Area Plating Material Finish	Matte
	1 μin

Termination Features

Termination Method to PCB	Surface Mount
Termination Post & Tail Length	3.93 mm[.16 in]

Mechanical Attachment

Connector Mounting Type	Board Mount
PCB Mount Retention Type	Kinked

Housing Features

Housing Material	PA 9T GF
Centerline (Pitch)	1 mm[.039 in]

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
PCB Thickness (Accepted)	1.57 mm[.062 in]
Connector Length	25 mm[.984 in]
Connector Height	10 mm[.394 in]
Connector Width	8.8 mm[.346 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Assembly Process Feature	Pick and Place Cover
Circuit Application	Signal

Industry Standards

Bus Type	PCI Express
PCI Generation	2 & 3

Packaging Features

Packaging Method	Box & Tray, Tray
Packaging Quantity	70



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-2337939-4
PCIE GEN4 CON,SMT,164POS,30u",
MYLAR,HT



TE Part # 1734774-1
PCI EXP 3.1L 36 POS WHT G/F


Customers Also Bought




TE Part #1586892-3
03P UMNL HDR ASSY R/A, GW V0



TE Part #1-2176349-7
CRGCQ 2512 220R 1%



TE Part #6-1614958-6
CPF 0805 4R64 0.1% 25ppm 1K RL



TE Part #9-216444-9
SUBASSY FOR 4/4 PCB MOD.JACK B



TE Part #1-1625868-6
RP 2A 0.25W 5K62 0.1% 25PPM 1K RL




TE Part #1-406525-1
IMJ,NO SHLD,8P,TRAY, SN



TE Part #2-1415899-2
RZ03-1C4-D012



TE Part #1825027-2
FSMRA1JH04=R/A,TACT PB SW,160G



TE Part #5-2176422-7
TLRP 2512 3.0W R018 1% 50PPM 4K RL



TE Part #9-146280-0
40 MODII HDR SRST B/A .100CL

Documents

Product Drawings
PCI EXP STRADDLE 36P BLK 1u"
English

CAD Files
Customer View Model
ENG_CVM_CVM_5-1734857-1_B.2d_dxf.zip
English
3D PDF
3D
Customer View Model
ENG_CVM_CVM_5-1734857-1_B.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_5-1734857-1_B.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



4-1773442-7 Card Edge Connector for PCI Express Applications

English

Product Specifications

Product Specification

English

Product Specification

English