

PRODUCT-DETAILS

# A44 352-100

A44 352-100 A44 352-100



## General Information

Extended Product Type	A44 352-100
Product ID	2CMA170537R1000
ABB Type Designation	A44 352-100
EAN	7392696705370
Catalog Description	A44 352-100 A44 352-100

Long Description

Advanced DIN-rail meter with a large and easy to read back lighted pixel-oriented display. The meter is intended for use in the industry, commercial buildings etc. The meter can be used in 3 or 4 wire systems with a wide voltage range. The meter has several instrumentation values, 25 possible alarms and event logs. Three phase transformer connected for active and reactive energy. Import and export of energy in different registers and one total. Resettable register for intermediate values. Up to four tariffs. Two outputs and inputs for pulses or alarm etc. RS-485 communication over Modbus RTU or EQ Bus. Accuracy class 0,5 (or C for MID meters). The meters is IEC approved + MID approved and verified.

## Technical

Standards	EN 50470-3
Product Name	A44 352-100
Function	Electricity meter
Sub-Function	Silver
Rated Voltage ( $U_r$ )	(Un) L-L 100 ... 500 V (Un) N-L 57.7 ... 288 V
Rated Current ( $I_n$ )	6 A
Current Rating	6 A
Frequency (f)	50 ... 60 Hz

	0.801 W
Communication Interface	Modbus
Accuracy	Active Energy Class $\pm 0,5\%$ (or C for MID meters). Reactive Energy Class $\pm 2\%$ .
Pulse Output Rate	1...999999
Number of Phases	3
Number of Counter Positions	7
ABB Type Designation	A44 352-100
Energy Meter Type	Effective Power Blind Power
Meter Type	Transformer connected
Mounting Type	DIN rail
Pulse Output Type	Electrical
Type of Indicator	Digital
Enclosure Material	Plastic
Communication	MODBUS RTU
Model Number	Measurement transformer
Connecting Capacity Main Circuit	0.5 ... 10 mm <sup>2</sup>

## Environmental

Ambient Air Temperature	Operation -40 ... 70 °C
Degree of Protection	IP20
RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Environmental Information	2CMC484005D0001

## Dimensions

Width in Number of Modular Spacings	7
Product Net Width	123 mm
Product Net Height	26.5 mm
Product Net Depth / Length	65 mm
Product Net Weight	0.363 kg
Size	97X123X65

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	98 mm
Package Level 1 Height	68 mm
Package Level 1 Depth / Length	144 mm
Package Level 1 Gross Weight	0.453 kg
Package Level 1 EAN	7392696705370

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	90283019
E-Number (Finland)	6625019

E-Number (Sweden)	0980719
Country of Origin	Italy (IT)
Selling Unit of Measure	piece

### Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC484002D0001
Environmental Information	2CMC484005D0001
Instructions and Manuals	2CMC484003M0201
RoHS Information	2CMC484006

### Popular Downloads

Data Sheet, Technical Information	2CMC484001M0201
Instructions and Manuals	2CMC484003M0201

### Classifications

ETIM 6	EC001506 - Kilowatt-hour meter
ETIM 7	EC001506 - Kilowatt-hour meter
ETIM 8	EC001506 - Kilowatt-hour meter
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer
CN8	90283019
Object Classification Code	P

### Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
2CSG225995R1101	CT MAX 1000 Current transformer	CT MAX 1000	1	piece
2CSG226055R1101	CT MAX 1000 SELV Current transformer	CT MAX 1000 SELV	1	piece
2CSG225945R1101	CT MAX 300 Current transformer	CT MAX 300	1	piece
2CSG226005R1101	CT MAX 300 SELV Current transformer	CT MAX 300 SELV	1	piece
2CSG225955R1101	CT MAX 400 Current transformer	CT MAX 400	1	piece
2CSG226015R1101	CT MAX 400 SELV Current transformer	CT MAX 400 SELV	1	piece
2CSG225965R1101	CT MAX 500 Current transformer	CT MAX 500	1	piece
2CSG226025R1101	CT MAX 500 SELV Current transformer	CT MAX 500 SELV	1	piece
2CSG225975R1101	CT MAX 600 Current transformer	CT MAX 600	1	piece
2CSG226035R1101	CT MAX 600 SELV Current transformer	CT MAX 600 SELV	1	piece
2CSG225985R1101	CT MAX 800 Current transformer	CT MAX 800	1	piece
2CSG226045R1101	CT MAX 800 SELV Current transformer	CT MAX 800 SELV	1	piece
2CSG225785R1101	CT PRO XT 100 Current transformer	CT PRO XT 100	1	piece
2CSG225885R1101	CT PRO XT 100 SELV Current transformer	CT PRO XT 100 SELV	1	piece
2CSG225795R1101	CT PRO XT 150 Current transformer	CT PRO XT 150	1	piece

2CSG225895R1101	CT PRO XT 150 SELV Current transformer	CT PRO XT 150 SELV	1	piece
2CSG225805R1101	CT PRO XT 200 Current transformer	CT PRO XT 200	1	piece
2CSG225905R1101	CT PRO XT 200 SELV Current transformer	CT PRO XT 200 SELV	1	piece
2CSG225815R1101	CT PRO XT 250 Current transformer	CT PRO XT 250	1	piece
2CSG225915R1101	CT PRO XT 250 SELV Current transformer	CT PRO XT 250 SELV	1	piece
2CSG225825R1101	CT PRO XT 300 Current transformer	CT PRO XT 300	1	piece
2CSG225925R1101	CT PRO XT 300 SELV Current transformer	CT PRO XT 300 SELV	1	piece
2CSG225745R1101	CT PRO XT 40 Current transformer	CT PRO XT 40	1	piece
2CSG225845R1101	CT PRO XT 40 SELV Current transformer	CT PRO XT 40 SELV	1	piece
2CSG225835R1101	CT PRO XT 400 Current transformer	CT PRO XT 400	1	piece
2CSG225935R1101	CT PRO XT 400 SELV Current transformer	CT PRO XT 400 SELV	1	piece
2CSG225755R1101	CT PRO XT 50 Current transformer	CT PRO XT 50	1	piece
2CSG225855R1101	CT PRO XT 50 SELV Current transformer	CT PRO XT 50 SELV	1	piece
2CSG225765R1101	CT PRO XT 60 Current transformer	CT PRO XT 60	1	piece
2CSG225865R1101	CT PRO XT 60 SELV Current transformer	CT PRO XT 60 SELV	1	piece
2CSG225775R1101	CT PRO XT 80 Current transformer	CT PRO XT 80	1	piece
2CSG225875R1101	CT PRO XT 80 SELV Current transformer	CT PRO XT 80 SELV	1	piece
2CCG000242R0001	SCU100 Control unit	SCU100	1	piece
2CDG110226R0011	QA/S3.16.1 Energy Analyzer, M-Bus, 16 Devices, MDRC	QA/S3.16.1	1	piece
2CDG110227R0011	QA/S3.64.1 Energy Analyzer, M-Bus, 64 Devices, MDRC	QA/S3.64.1	1	piece
2CDG110228R0011	QA/S4.16.1 Energy Analyzer, Modbus RTU, 16 Devices, MDRC	QA/S4.16.1	1	piece
2CDG110229R0011	QA/S4.64.1 Energy Analyzer, Modbus RTU, 64 Devices, MDRC	QA/S4.64.1	1	piece
2CDG110224R0011	QA/S1.16.1 Energy Analyzer, KNX, 16 Devices, MDRC	QA/S1.16.1	1	piece

---

## Categories

---

Low Voltage Products and Systems → Modular DIN Rail Products → Energy Efficiency Devices → Energy Meters

