


U.I. Lapp GmbH	PRODUCT INFORMATION	
	ÖLFLEX® ROBUST 215 C	12.09.2012

Proven all-weather control cables – resistant to a wide range of chemical media
 Outstanding weather, ozone and UV resistance together with the wide temperature range enable versatile use for both indoor and outdoor applications
 Resistant to contact with plant, animal or synthetic-based organic oils, greases, waxes and the related emulsions
 Good resistance to ammonia compounds and bio-gases
 Good resistance to cold and hot water as well as water-soluble cleaning agents
 Well-suited to frequent steam cleaning



Info

Excellent weather resistance
 High chemical resistance
 EMC compliant copper screening

Application range

Machine tool building, medical technology, laundries, car washing equipment, chemical industry, composting plants, sewage works
 Food and beverage industry, especially for production and processing equipment of milk and meat products
 For indoor and outdoor use
 In EMC-sensitive environments (electromagnetic compatibility)

Design

Fine-wire strand made of bare copper wires
 Core insulation made of modified PP
 Cores twisted in layers
 Halogen-free plastic foil wrapping
 Tinned copper screen braiding
 Outer sheath made of special TPE
 Sheath colour: black (RAL 9005)


Product features

Halogen-free materials
 Good chemical resistance to ester-based hydraulic fluids
 Ozone, UV and weather-resistant according to EN 50396 and HD 605 S2
 Flexible down to -40 °C
 Number-coded cores

Remark

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.
 Copper price basis: EUR 150/100kg. Refer to Appendix T17 for the definition and calculation of copper-related surcharges.
 Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths
 Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum
 Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).
 Single lengths for sizes: ≥ 4G16 max. 600 m; ≥ 4G25 max. 300 m; ≥ 4G50 max. 250 m
 Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: LAPP_PRO31EN.pdf	1 / 5
--------------------	----------------------------	-------

U.I. Lapp GmbH	PRODUCT INFORMATION	 LAPP GROUP
	ÖLFLEX® ROBUST 215 C	12.09.2012

Technical Data

Core identification code:	Black with white numbers acc. to VDE 0293
Based on:	VDE 0250/0281
Conductor stranding:	Fine wire according to VDE 0295, class 5/IEC 60228 class 5
Minimum bending radius:	Occasional flexing: 20 x outer diameter Fixed installation: 6 x outer diameter
Nominal voltage:	U ₀ /U: 300/500 V
Test voltage:	Core/core: 4000 V Core/screen: 2000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	Occasional flexing: -40°C to +80°C Fixed installation: -50°C to +80°C

Product Management	Document: LAPP_PRO31EN.pdf	2 / 5
--------------------	----------------------------	-------

ÖLFLEX® ROBUST 215 C

12.09.2012

Part number	Number of cores and mm ² per conductor	Outer diameter (mm)	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® ROBUST 215 C				
0022700	2 X 0,5	5,9	36.0	42
0022701	3 G 0,5	6,2	43.0	52
0022702	3 X 0,5	6,2	43.0	52
0022703	4 G 0,5	6,6	49.0	59
0022704	4 X 0,5	6,6	49.0	59
0022705	5 G 0,5	7,1	57.0	68
0022706	5 X 0,5	7,1	57.0	68
0022708	7 G 0,5	7,7	69.0	85
0022709	7 X 0,5	7,7	69.0	85
0022711	12 G 0,5	10,1	104.0	136
0022712	18 G 0,5	11,8	141.0	189
0022713	25 G 0,5	13,7	211.0	265
0022717	2 X 0,75	6,3	43.0	50
0022718	3 G 0,75	6,6	52.0	60
0022719	3 X 0,75	6,6	52.0	60
0022720	4 G 0,75	7,1	61.0	72
0022721	4 X 0,75	7,1	61.0	72
0022722	5 G 0,75	7,9	72.0	88
0022723	5 X 0,75	7,9	72.0	88
0022724	7 G 0,75	8,5	89.0	110
0022725	7 X 0,75	8,5	89.0	110
0022727	12 G 0,75	11,1	138.0	177
0022728	18 G 0,75	13.0	211.0	247
0022729	25 G 0,75	15,1	280.0	347
0022730	34 G 0,75	17,5	380.0	460
0022733	2 X 1,0	6,6	51.0	60
0022734	3 G 1,0	6,9	62.0	70
0022735	3 X 1,0	6,9	62.0	70
0022736	4 G 1,0	7,4	74.0	85
0022737	4 X 1,0	7,4	74.0	85
0022738	5 G 1,0	8,3	88.0	103

Part number	Number of cores and mm ² per conductor	Outer diameter (mm)	Copper index (kg/km)	Weight (kg/km)
0022739	5 X 1,0	8,3	88.0	103
0022740	7 G 1,0	8,9	112.0	131
0022742	12 G 1,0	11,7	185.0	213
0022743	18 G 1,0	14,1	268.0	321
0022744	25 G 1,0	16,2	354.0	425
0022748	2 X 1,5	7,2	65.0	71
0022749	3 G 1,5	7,6	82.0	90
0022750	3 X 1,5	7,6	82.0	90
0022751	4 G 1,5	8,4	100.0	114
0022752	4 X 1,5	8,4	100.0	114
0022753	5 G 1,5	9,1	119.0	136
0022754	5 X 1,5	9,1	119.0	136
0022756	7 G 1,5	10,0	154.0	177
0022757	7 X 1,5	10,0	154.0	177
0022760	12 G 1,5	13,4	268.0	290
0022761	18 G 1,5	15,8	373.0	435
0022762	25 G 1,5	18,2	530.0	579
0022763	34 G 1,5	21,2	683.0	797
0022767	3 G 2,5	9,1	118.0	134
0022768	4 G 2,5	10,0	147.0	169
0022769	5 G 2,5	11,1	176.0	207
0022770	7 G 2,5	12,0	253.0	270
0022774	4 G 4	11,9	190.0	258
0022776	4 G 6	14,5	290.0	392
0022777	4 G 10	17,5	458.0	602
0022778	4 G 16	20,2	736.6	928
0022771	4 G 25	25,1	1126.7	1411

U.I. Lapp
GmbH

PRODUCT INFORMATION



LAPP GROUP

ÖLFLEX® ROBUST 215 C

12.09.2012

Part number	Number of cores and mm ² per conductor	Outer diameter (mm)	Copper index (kg/km)	Weight (kg/km)
0022780	4 G 35	28.0	1540.0	1883

Product Management

Document: LAPP_PRO31EN.pdf

5 / 5