

Features

- Miniature housing
- Sensitivity adjustment via potentiometer
- IO-Link
- Calibrated range
- Immunity to mutual interferences

RS PRO Photoelectric Sensor

RS Stock No.: 0360257



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- Miniature housing
- Sensitivity adjustment via potentiometer
- IO-Link
- Calibrated range
- Immunity to mutual interferences

General Specifications

Detection Type	Diffuse
Sensing/Detection Range	3 ... 1500 mm
Operating Distance	5 ... 1200 mm
Standard Sensing Object	Object with 90% reflectance (standard white paper)
Light Source	Red LED
Diameter of the Light Spot	Ø 15 mm (500 mm)/Ø 26 mm (1 m)
Sensing Distance Adjustment	30 ... 1500 mm, 3/4-turn pot
Output Type	PNP / Light-on/IO-Link
Response Time	≤ 340 us (normal)/≤ 1 ms (fine) / ≤ 100 us (fast)
Connection/Terminal Type	PVC
Indicator	LED
Interface	IO-Link
Wiring Technique	3 wire
Minimum Operating Temperature	-25°C
Maximum Operating Temperature	+65°C

Electrical Specifications

Operating Supply Voltage	10 ... 30 VDC
Current Consumption	≤ 100 mA
Voltage Drop	$\leq (U_b - 2.0 \text{ V})/\text{approx. } 0 \text{ V}$
Maximum Switching Frequency	≤ 5 kHz
Reverse Polarity Protection	YES
Overload Protection	YES
Short Circuit Protection	YES

Mechanical Specifications

Body Style	Rectangular
Mounting Type	Screw
Housing Material	ABS
Lens/Face Material	PMMA
Dimensions	20 x 30 x 10 mm
Width / Diameter	10 mm
Length	30 mm
Depth	20 mm
Weight	16 g
Shock Resistance	IEC 60947-5-2
Vibration Resistance	IEC 60947-5-2

Protection Category

IP Rating	IP67
-----------	------

Approvals

Compliance/Certifications	CE / CULus / ECOLAB
---------------------------	---------------------

