



Connectors > RF Connectors > Coax Connectors > MMCX Jack Connector: 50 Ohm Impedance



RF Interface: **MMCX**

RF Connector Style: **Jack**

RF Connector Mated Outer Diameter (Approximate): **2.43 mm [ .096 in ]**

Impedance: **50 Ω**

RF Connector Coupling Mechanism: **Push-On**

[All MMCX Jack Connector: 50 Ohm Impedance \(0\)](#)

Features

Product Type Features

RF Interface	MMCX
RF Connector Style	Jack
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Body Material	Brass
---------------	-------



Body Plating Material	Gold
-----------------------	------

Contact Features

RF Connector Center Contact Underplating Material	Nickel
RF Connector Center Contact Plating Material	Gold (Au)
RF Connector Center Contact Material	Beryllium Copper

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	3 mm[.118 in]

Mechanical Attachment

RF Connector Coupling Mechanism	Push-On
Connector Mounting Type	Board Mount
RF Contact Captivation Method	Mechanical
Detent	Without

Dimensions

Profile Height from PCB	3.8 mm[.15 in]
RF Connector Mated Outer Diameter (Approximate)	2.43 mm[.096 in]

Operation/Application

Operating Frequency	6 GHz
---------------------	-------

Packaging Features

Packaging Quantity	100
Packaging Method	Package

Other

Dielectric Material	PTFE
---------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2021 (219)



SVHC > Threshold:  
Pb (3.7% in Component Part)

Article Safe Usage Statements:  
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.


Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
-----------------	--

Solder Process Capability	Pin-in-Paste capable to 260°C
---------------------------	-------------------------------


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #CAT-AM74-UN384H  
AMP-LATCH UNIVERSAL HEADERS




TE Part #1-206070-1  
CABLE CLAMP KIT #17




TE Part #5-102523-3  
05 MODII HDR SRRA SHRD .100CL




TE Part #5-1879061-5  
CPF 0402 1K5 0.1% 25PPM 5K RL



TE Part #2227302-1  
CAGE ASSY, PRESS FIT, SFP



TE Part #1-1617146-5  
JMGACD-26PW = M39016/18-042P



TE Part #206044-1  
CPC PLUG ASSEMBLY SIZE 17-14



TE Part #5-1879061-1  
CPF 0402 1K0 0.1% 25PPM 5K RL



Documents

Product Drawings

MMCX PCB RIGHT ANGLE JACK THRU

English

CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1408151-1\\_C.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1408151-1\\_C.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1408151-1\\_C.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

MCX Connectors

English

Product Specifications

Application Specification

English