



Technical data

4T-HM807048

Single row tapered roller bearings

Mounted cone, pressed steel cage

VISUAL (S)



4T-HM807048

Single row tapered roller bearings

PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	54,488 mm
B - Bearing/Inner ring width	36,512 mm
d1 - External diameter inner ring	81,5 mm

PRODUCT PERFORMANCE

C - Dynamic load	153000000 mN
C0 - Static load	189000000 mN
A2 - Rating life coefficient	1
e - Coefficient	0.49
Y0 - Static axial load coefficient	0.68
Y2 - Upper axial load coefficient	1.23

ABUTMENT

da max - Max shoulder diameter IR	63 mm
db min - Min IR shoulder diameter	73 mm
ra max - Max fillet radius	3,5 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$P_0 = X_0.F_r + Y_0.F_a$

X_0	Y_0
0.5	Y0

If $P_0 \leq F_r$, then use $P_0 = F_r$

The values for e, Y2 and Y0 are shown in the above table

