

## Completely pre-assembled Signal Towers / KOMPAKT 37

## K37 plug EM Pulse tone 24VAC/DC BU/CL/GN



| Part No.: | 699.260.75 |
|-----------|------------|
| Series:   | Kompakt 37 |



| MECHANICAL DATA             |   |
|-----------------------------|---|
| Height                      | 243 mm                                  |
| Diameter                    | 38 mm                                   |
| Materials                   | PC                                      |
| Dome colour                 | Blue<br>Clear<br>Green<br>Red<br>Yellow |
| Housing colour              | Black                                   |
| Protection category         | IP65                                    |
| Connection                  | M12 plug 8-pole                         |
| Cable entry                 | Membrane grommet                        |
| Cable entry minimum         | d = 1 mm                                |
| Cable entry maximum         | d = 9 mm                                |
| Tension relief              | Pull-out protection                     |
| Type of fixing              | Built-in mounting                       |
| Working temperature minimum | -20°C                                   |
| Working temperature maximum | +50°C                                   |
| UL Type Rating              | Type 12<br>Type 4X                      |
| Weight with packaging       | 173 g                                   |
| Product weight              | 119 g                                   |

| ELECTRICAL DATA             |                           |
|-----------------------------|---------------------------|
| Operating voltage           | 24V                       |
| Operating voltage type      | AC/DC                     |
| Operating voltage frequency | 50Hz                      |
| Operating voltage tolerance | +/- 10%                   |
| Rated operational voltage   | 24 VDC                    |
| Rated operational current   | 200 mA                    |
| Rated inrush current        | 500 mA                    |
| Protection class            | Protection class 2        |
| Pollution degree            | In the connection area: 2 |

| OPTICAL DATA |     |
|--------------|-----|
| Light source | LED |

For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.




## Completely pre-assembled Signal Towers / KOMPAKT 37

## K37 plug EM Pulse tone 24VAC/DC BU/CL/GN

| Light colour         | Blue<br>Green<br>Red<br>White<br>Yellow |
|----------------------|---|
| Optical signal image | Permanent                               |
| Service life optical | 50,000 h maximum                        |

| ACUSTICAL DATA                |                 |
|-------------------------------|-----------------|
| Volume/dB(max) at 1m distance | 85,0 dB (A)     |
| Acoustic signal image         | Pulse tone      |
| Audio frequency               | 2900 Hz         |
| Acoustic service life         | 5,000 h minimum |



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.