


10. ACCESSORIES (continued)

10.4 19" lighting kit

The kit Cat. No. 0 464 85 consists of a 1U 19" panel equipped with a fluorescent light.



Features


- Quick screw-free fixing on 2 x 19" uprights
- Class I
- IP20
- ON/OFF switch
- 230 V~ - 50Hz power supply
- Ferromagnetic ballast
- Rear connection on terminal block
- For Ø 16 mm fluorescent tube, length 288 mm, G13 cap
- Supplied with 8 W white tube
- Panel 1.5 mm thick steel + black RAL 9005 finish

11. 19" EQUIPMENT

11.1 19" management panels

For ease of mounting, the 19" LCS² panels incorporate a quick fixing:

- The plastic panels clip on directly. The only tool required is a flat screwdriver for their removal (see section 7.1).
- The metal panels are equipped with 2 ergonomic fixings that do not require any screws or tools.




The quick fixing for metal panels is compatible with 1.4 to 2.75 mm thick 19" uprights with 8.25 to 9.5 mm square perforations. An automatic equipotential link is ensured with 19" LCS² uprights. Direct clipping on of plastic panels is compatible with 1.5 to 2 mm thick 19" uprights with 9.5 mm square perforations.

11. 19" EQUIPMENT (continued)

11.1 19" management panels (continued)


11.1.1 Management panels with 2 axes

- Metal panels with quick fixing
- Horizontal and front to back feedthrough
- Plastic cable management rings radiating out (to protect cords and maintain the bending radius)



Cat. No.	Panels with 2 axes	Depth (mm)	Dimensions of feedthroughs (mm)	Rings usable cross-section (mm ²)
0 465 22	Metal 1U	90	30 x 60	1890
0 465 23	Metal 2U	90	65 x 60	4070


- Excellent resistance to unclipping under the weight of cables and cords



- Panels 1.5 mm thick steel
- Polyamide rings
- Zamak quick fixing
- Black RAL 9005

11.1.2 Management panels with brushes

- Direct clip-on plastic panels



- Metal panels with quick fixing

