


P-15

LONG NOSE PLIERS WITH SIDE CUTTER

P-15-125


P-15-150



These pliers feature induction hardened jaws for long lasting use.


- Max. cutting capacity: 2.6mm dia. copper wire.
- Hardness: HRC58 (cutting section)
- Weight: P-15-125 : 95g

P-15-150 : 125g



() is size 150

P-15-150




ELASTOMER GRIPS

Soft plastic, no-slip handle grips.

P-22


LONG NOSE PLIERS WITH SIDE CUTTER



Induction hardened, serrated jaws provide for long lasting grip.

- Multipurpose use for cutting, bending and forming of wire.

- Max. cutting capacity: 2.6mm dia. copper wire.
- Hardness: HRC58 (cutting section)
- Weight: 125g




With serration



ELASTOMER GRIPS


P-17

NEEDLE JAW PLIERS WITH SIDE CUTTER



These long, thin nosed pliers have excellent gripping capability especially in tight, narrow areas.

- Max. cutting capacity: 2.6mm dia. copper wire.
- Hardness: HRC58 (cutting section)
- Weight: 90g



With serration




ELASTOMER GRIPS

P-12

BENT NOSE PLIERS

These thin nosed profile pliers get into tight places and make it easy to reach in obstructed areas.

- Hardness: HRC45
- Weight: 115g



ELASTOMER GRIPS


P-16

FLAT NOSE PLIERS



Flat rectangular jaw for firm gripping of flat objects.

- Hardness: HRC45
- Weight: 115g



ELASTOMER GRIPS