

# Eaton 265284

Catalog Number: 265284

Eaton Distribution parts. Impulse relay, 110AC, 1 N/O, 1 N/C, 16A, 50Hz, 1HP

General specifications



Product Name  
Eaton Distribution parts

Catalog Number  
265284

EAN  
4015082652845

Product Length/Depth  
80 mm

Product Height  
70 mm

Product Width  
17.5 mm

Product Weight  
0.136 kg

Compliances  
RoHS conform

## Product specifications

### Mounting method

DIN rail

### Control voltage 1 type

AC

### Ambient operating temperature - max

45 °C

### Ambient operating temperature - min

-20 °C

### Control voltage 1 - max

110 V

### Control voltage 1 - min

110 V

### Control voltage 2 - max

0 V

### Control voltage 2 - min

0 V

### Frequency control voltage 1 - max

50 Hz

### Frequency control voltage 1 - min

50 Hz

### Frequency control voltage 2 - max

0 Hz

### Frequency control voltage 2 - min

0 Hz

### Heat dissipation per pole, current-dependent

1.5 W

### Incandescent lamp load - max

2024 W

### Load fluorescent lamp - max

2500 VA

### Load fluorescent lamp (duo circuit) - max

2500 VA

### Load fluorescent lamp (parallel compensated) - max

2500 VA

### Number of contacts (change-over contacts)

## Resources

### Declarations of conformity

[DA-DC-03\\_Z-S](#)

[DA-DC-03\\_Z-S\\_SC\\_SB](#)

### Drawings

[eaton-wiring-diagram-z-s-1te.jpg](#)

[eaton-dimensions-mas-z-s230.jpg](#)

[eaton-3d-drawing-z-s230-scha2.jpg](#)

0

Number of contacts (normally closed contacts)

1

Number of contacts (normally open contacts)

1

Rated operational current for specified heat dissipation (In)

16 A

Rated switch current

16 A

Equipment heat dissipation, current-dependent

3 W

Supply voltage - max

240 V

Supply voltage - min

24 V

Switching current (cos phi = 0.6) - max

24 A

Width in number of modular spacings

1

Built-in depth

60 mm

Operating mode

Manual operation possible

Control voltage 2 type

AC

Voltage type

AC

Functions

Mechanical switch



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)