
solenoid valve VUVS-LK30-B52-D-G38-1B2-S Part number: 8049882 ★ Core product range







Data sheet

Feature	Value
Valve function	5/2 bistable
Type of actuation	electrical
Valve size	31 mm
Standard nominal flow rate	1,600 l/min
Operating pressure	1.5 8 bar
Design structure	Piston slide
Protection class	IP65
Troccus in class	to IEC 60529
	with plug socket
Nominal size	8.1 mm
Exhaust-air function	throttleable
Sealing principle	soft
Assembly position	Any
Manual override	detenting
i idilidai override	Pushing
Type of piloting	Piloted
Pilot air supply	Internal
Flow direction	non reversible
Overlap	Positive overlap
b value C value	0.37
	7.03 l/sbar
Switching time reversal	10 ms
Duty cycle	100%
Max. positive test pulse with logic 0	2,500 µs
Max. negative test pulse with logic 1	1,100 µs
Characteristic coil data	24 V DC: 3.3 W
Permissible voltage fluctuation	+/- 10 %
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Vibration resistance	Transport application test at severity level 2 in accordance with FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 1 in accordance with FN 942017-5 and EN 60068-2-27
Corrosion resistance classification CRC	1 - Low corrosion stress
Medium temperature	-5 50 °C
Pilot medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Ambient temperature	-5 50 °C
Product weight	392 g
Electrical connection	Plug pattern type B to EN 175301-803
Mounting type	Optional
risultaring type	on manifold rail
	with through hole
Scavenging orifice connection	Non-ducted
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 2	G3/8
i neamade connection, port 2	100/0



Feature	Value
Pneumatic connection, port 3	G3/8
Pneumatic connection, port 4	G3/8
Pneumatic connection, port 5	G3/8
Materials note	Contains PWIS substances
	Conforms to RoHS
Material seals	HNBR
	NBR
Material housing	Wrought Aluminium alloy
Material Piston slide	Wrought Aluminium alloy