



Connectors > Rectangular Connectors > Standard Rectangular Connectors > AMP COMMON TERMINATION HOUSINGS



Connector Product Type: **Connector Assembly**
Connector System: **Wire-to-Board**
Number of Positions: **10**
Centerline (Pitch): **2 mm [.079 in]**
Number of Rows: **1**

[All AMP COMMON TERMINATION HOUSINGS \(176\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	10
Number of Rows	1

Contact Features

Contact Current Rating (Max)	2 A
------------------------------	-----

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Housing Material	PBT GF
Centerline (Pitch)	2 mm[.079 in]

Dimensions

	2 in
--	------



Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 3-292254-0
CT RELAY HDR ASSY 10P BLUE



TE Part # 3-292145-0
CT P/HDR ASSY V 10P W/O KINK B




TE Part # CAT-3983178-PHBXVD
CT 2mm Post Header Asmbly: Box V DIP



TE Part # 3-173985-0
CT AMP-IN ASSY 10P V BLUE




TE Part # 58372-1
HEAD (IDC) 2MM C.T. W/O TL




TE Part # 6-292271-0
MT REC ASSY AU-PL. 10P BLUE




TE Part # CAT-3980407-RHDRRA
CT 2mm Header Assembly: Right Angle




TE Part # 3-292170-0
CT P/HDR ASSY 10P V W/O KINK



TE Part # 3-292165-0
CT P/HDR BOX V 10P T/P BLUE



TE Part # CAT-3983174-PHBXHK
CT 2mm Post Header Assembly Box H Kink



TE Part # 3-292164-0
CT P/HDR BOX H ASSY 10P T/P BL



TE Part # 1-292254-0
CT RELAY HDR ASSY 10P NAT



TE Part # CAT-3980408-PHDWKV
CT 2mm Post Header Assembly with Kink - Vertical




TE Part # 58074-1
MTA 50/100/156 MANUAL TOOL FRAME


Also in the Series | AMP CT



Connector Contacts(8)



Connector Hardware(46)



PCB Headers & Receptacles(756)



Rectangular Connector Housings(72)



Rectangular Power Connectors(906)



Standard Rectangular Connectors(158)



Wire-to-Board Connector Assemblies & Housings(97)



Wire-to-Board Headers & Receptacles (756)


Customers Also Bought




TE Part #CAT-AM7017-H8172
AMP COMMON TERMINATION HOUSINGS



TE Part #1-2355088-1
MICRO CT CONN MT REC ASSEMBLY 11P




TE Part #3-292216-8
MINI CT D/R RELAY 38P V NAT



TE Part #2-292216-2
MINI CT D/R RELAY 22P V NAT



TE Part #1-2355088-9
MICRO CT CONN MT REC ASSEMBLY 19P



TE Part #1123907-1
1.5 MINI CT LATTICE POWER REC



TE Part #6-292254-2
CT RELAY HDR ASSY 2P BLACK



TE Part #F31612-000
NC-254097-10-9



TE Part #9-292112-4
MT REC ASSY (#26,28)

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_3-173977-0_M.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-173977-0_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-173977-0_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets



MINI PRESS CT CONNECTOR (WAS IS-553J)

Japanese

Instruction Sheet (non U.S.)

Japanese

Agency Approvals

CSA Certificate

English

CSA Certificate

English