



DEWALT Stainless Steel Cutting Circular Saw Blade –

140mm 40T

DT1918 -QZ



- Designed to power through stainless steel with ease, DeWALT stainless steel Metal Cutting™ saw blades are crafted from carbide for long life and less chipping. Each blade is laser-etched and color-coded by material
- Each blade is laser etched and color coded by material

Description:

The range of metal cutting blades are optimised for cutting steel, aluminum or stainless steel. Through a proprietary in-house process tooth alignment has reached a level to give a smooth accurate cut, minimizing vibration and burring.

| Specifications | |
|-----------------|------------------------------------|
| Diameter | 140mm |
| Bore Size | 20mm |
| Plate Thickness | 1.13mm |
| Kerf Thickness | 1.53mm |
| Tooth Count | 40 |
| Grind | Modified Triple Chip Grind + Raker |
| Rake Angle | 10 ° |
| Tooth Direction | Clockwise |