

AeraMax® Pro AM3 PC CLEANS UP TO 55M²

REMOVES OVER 99.99% OF COVID-19*

In a recent test, **Fellowes AeraMax Pro air purifiers** demonstrated to **eliminate COVID-19[†]**, using a combination of smart and integrated technologies
- **only from Fellowes.**

SPECIFICATIONS

System Dimensions (HxWxD)	495 x 534 x 241 mm
Weight of system (including filters)	9.1kg
Air Flow, 5 speeds (m ³ /h)	129, 158, 190, 238, 374
Sound pressure levels, each fan speed (dB)	31, 36, 40, 47, 55
Power Requirements	220-240V, 50/60Hz, 0.9A
Power Consumption (W)	7, 10, 14, 24, 105
Electrical Safety certification	TUV, GS, CE
Ozone testing certification	UL2998: Report 1001231822-3923572
Motor	Single motor: encased brushless DC motor, thermal and overcurrent protection, designed for low noise, long-term continuous use at high RPM
Air intake / outlet	Bottom / Top
Control panel	Capacitive touch, internal access only
Housing material	UV stabilized ABS
Operating temperature / humidity level	5-40°C / Up to 60%
Area Coverage	30-55m ²
Warranty	5-Year Limited Warranty



PureView's patented sensor technology and display makes the invisible visible with real time status updates as the air is cleaned. It provides **maximum peace of mind** that the air you and others breathe is clean.



Wall mount

Floor stand

CONFIGURATIONS

	Code	Dimensions
Wall mount	9573801	495 x 534 x 241 mm
Floor stand	9574001	576 x 530 x 270 mm




	Standard Filter Configuration	Hybrid Filter	Full Carbon Filter (High Odour/VOC)	Pre-Filters
Filter Type	10mm Carbon Filter (w/pre-filter) 50mm H13 HEPA	60mm filter containing 50% Carbon & 50% True HEPA	60mm Carbon Filter (w/pre filter)	Replacement Pre-Filter
Estimated Filter Life	Carbon: 6 Months H13 HEPA: 12 Months	12 Months	12 Months	6-12 Months
Pack Size	Carbon: 4 Pack H13 HEPA: 2 Pack	2 Pack (ships with pre-filters)	2 Pack	4 Pack
Item Numbers	Carbon: 9416502 H13 HEPA: 9416602	9436902	9436802	9600501

AeraMax Pro AM3 PC

Recyclability:

Percentage of this product and packaging that can be easily separated for recycling



Energy Usage:

Fan Speed	1	2	3	4	5	Automatic Mode (AVG 1-4)
Annual kWh	43.80	70.08	96.36	183.96	876.00	98.55

The average annual running cost based on 24/7 running time is **€20.70**, based on an energy price calculated at €0.21 per kWh, which is the average electricity price across Europe as of July 2022*. This is less than half the cost of running a fridge-freezer with an energy rating of A.**

*<https://strom-report.de/electricity-prices-europe/>

**<https://www.confused.com/gas-electricity/guides/appliances-how-much-do-yours-cost-to-run>

Aftercare:

Servicing:

Based on the standard filter configuration, the 50mm H13 Filter needs to be replaced every 12 months and the 10mm Carbon Filter every 6 months. For the other filter configurations, please check filter life before use.

Cleaning:

Wipe over with a damp microfibre cloth. Do not use any cleaning solutions.

Handling & Storage:

Read and follow all instructions and warnings before use. This product is intended for indoor use only.

Support:

This unit comes with a 5-year warranty. For product related questions, or further information, our dedicated Customer Service team can be reached at our freephone number 00800 1810 1810.