
Features

- Scissor-action mechanism for secure and easy placement around lockout points.
- 38mm Jaw Size to accommodate lockout requirements.
- Supports up to 6 padlocks with compatibility for shackle diameters up to 8.5 mm
- High-quality aluminium die-cast construction ensures durability in industrial environments.
- Vinyl-coated padlock fixing section provides enhanced grip and high visibility.
- Simple fit-and-lock design for quick and reliable application during lockout procedures.

RS PRO Aluminium Lockout Tagout Hasp - 38mm

RS Stock No.: 0802204



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *A versatile scissor-action lockout hasp designed to isolate energy sources during maintenance and safety procedures securely.*
- *Enables multiple workers to apply their personal padlocks, ensuring group lockout compliance and improved safety.*
- *38mm Jaw Size to fit a broad range of lockout points commonly found in industrial setups.*
- *Made from rugged aluminium die casting to endure tough working environments and long-term daily use.*
- *Features a vinyl-coated padlock fixing section to enhance grip, reduce slipping, and improve visibility during application.*
- *Ideal for mechanical, electrical, and industrial workplaces requiring dependable lockout devices to meet safety protocols.*

General Specifications

Type	Lockout Hasp
Material	Aluminium with Vinyl Coating
Colour	Red
Padlock holes	06
Package	Individual Box

Mechanical Specifications

Dia (Jaw Size)	38mm
Width	50mm
Height	126mm
Shackle Dia	6mm
Accepted Shackle Diameter	8.5mm
Weight	44 Grams

Operation Environment Specifications

Withstand temperature	-20°C to +80°C


ON
OFF
MCCB TP 25KA
INCOMER-1
VOLTMETER
1 PHASE
428.6