


SUH400



Ultrasonic flow meter

SUC501JBFRKG/US



Product characteristics				
Measuring range	5...1000 l/min	300...60000 l/h	0.058...11.666 m/s	0.3...60 m³/h
Nominal diameter	DN50 (2")			
Process connection	Clamp 2" DIN 32676 series C (ASME BPE)			
Application				
Special feature	Gold-plated contacts			
Media	ultra-pure water; water; hydrous media; edible oils			
Note on media	hydrous media: for media with >10 % additives, the repeatability is the only available value edible oils: palm oil, soy oil, rapeseed oil, sunflower oil, peanut oil, olive oil and others			
Medium temperature [°C]	-20...100			
Min. burst pressure	75 bar	7.5 MPa		
Pressure rating	25 bar	2.5 MPa		
Note on pressure rating	take into account the pressure resistance of the bracket and the seal used for clamp connection			
Vacuum resistance [mbar]	-1000			

SUH400



Ultrasonic flow meter

SUC501JBFRKG/US

Electrical data				
Operating voltage	[V]	18...32 DC; (to SELV/PELV)		
Current consumption	[mA]	< 75		
Protection class		III		
Reverse polarity protection		yes		
Power-on delay time	[s]	5		
Measuring principle		ultrasonic		
Inputs / outputs				
Total number of inputs and outputs	2			
Inputs				
Inputs	OUT2	counter reset		
Outputs				
Total number of outputs	2			
Output signal	OUT1	switching signal; pulse signal; diagnostic signal; totaliser switching signal; frequency signal; IO-Link		
	OUT2	switching signal; pulse signal; diagnostic signal; totaliser switching signal; analogue signal		
Electrical design	PNP/NPN			
Min. load resistance	[Ω]	2000		
Pulse output	flow rate meter			
Short-circuit protection	yes			
Type of short-circuit protection	pulsed			
Overload protection	yes			
Analogue				
Number of analogue outputs	1			
Analogue current output	[mA]	4...20		
Max. load	[Ω]	500		
Digital				
Number of digital outputs	2			
Output function	normally open / normally closed; (parameterisable)			
Max. voltage drop switching output DC	[V]	2		
Permanent current rating of switching output DC	[mA]	100		
Switching frequency DC	[Hz]	0...10000		
Measuring/setting range				
Measuring range	5...1000 l/min	300...60000 l/h	0.058...11.666 m/s	0.3...60 m³/h
Display range	-1200...1200 l/min	-72000...72000 l/h	-13.999...13.999 m/s	-72...72 m³/h
Resolution	0.1 l/min	1 l/h	0.001 m/s	0.002 m³/h
Set point SP	10.5...1000 l/min	630...60000 l/h	0.122...11.666 m/s	0.63...60 m³/h
Reset point rP	5.3...994.8 l/min	318...59688 l/h	0.062...11.605 m/s	0.318...59.688 m³/h
Analogue start point ASP	-1000...800 l/min	-60000...48000 l/h	-11.666...9.333 m/s	-60...48 m³/h
Analogue end point AEP	-800...1000 l/min	-48000...60000 l/h	-9.333...11.666 m/s	-48...60 m³/h

SUH400



Ultrasonic flow meter

SUC501JBFRKG/US

Low flow cut-off LFC	5...50 l/min	300...3000 l/h	0.058...0.583 m/s	0.3...3 m³/h
Frequency end point, FEP	200.6...1000 l/min	12037...60000 l/h	2.34...11.666 m/s	12.037...60 m³/h
Frequency at the end point FRP [Hz]	1...10000			
Volumetric flow quantity monitoring				
Pulse length [s]	0.002...2			
Pulse value	0.1...99990000 l			
Temperature monitoring				
Measuring range [°C]	-20...100			
Display range [°C]	-44...124			
Resolution [°C]	0.1			
Set point SP [°C]	-19.6...100			
Reset point rP [°C]	-20...99.6			
Analogue start point [°C]	-20...76			
Analogue end point [°C]	4...100			
Frequency start point, FSP [°C]	-20...76			
Frequency end point, FEP [°C]	4...100			
Frequency at the end point FRP [Hz]	1...10000			
Accuracy / deviations				
Flow monitoring				
Accuracy (in the measuring range)	edible oils		± (5,0 % MW + 1,0 % MEW)	
	water		± (1,0 % MW + 0,5 % MEW)	
Repeatability	± 0,2 % MEW			
Temperature monitoring				
Accuracy [K]	± 2,5 (Q > 5 % MEW)			
Temperature coefficient [% of the span / 10 K]	0,2			
Response times				
Flow monitoring				
Response time [s]	< 0.25; (dAP = 0, T09)			
Damping process value dAP [s]	0...5			
Temperature monitoring				
Dynamic response T05 / T09 [s]	5,7 / 86			
Software / programming				
Diagnostic functions	direction of flow detection; signal quality			
Interfaces				
Communication interface	IO-Link			
Transmission type	COM2 (38,4 kBaud)			
IO-Link revision	1.1.3			
SDCI standard	IEC 61131-9: 2013-07			
Profiles	BLOB		Binary Large Object transfer	
	Common - I&D		Identification and Diagnosis	
Required master port type	A			

SUH400



Ultrasonic flow meter

SUC501JBFRKG/US

Process data analogue		3
Process data binary		2
Min. process cycle time	[ms]	9.6
IO-Link process data (cyclical)	function	bit length
	totaliser	32
	Flow monitoring	32
	Temperature monitoring	32
	status	4
	Output 1	1
	Output 2	1
Supported DeviceIDs	Type of operation	DeviceID
	default	1752

Operating conditions

Ambient temperature	[°C]	-20...60
Storage temperature	[°C]	-25...80
Protection		IP 69K

Tests / approvals

EMC	DIN 61326-1:2021	
CPA approval	model number	003US
	accuracy class	1,5
Shock resistance	DIN IEC 68-2-27	20 g (11ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000Hz)
MTTF	[years]	160
UL approval	UL approval no.	I033
	File number UL	E174189
Pressure Equipment Directive	can be used for group 2 fluids; group 1 fluids on request	

Mechanical data

Weight	[g]	933
Housing		rectangular
Inlet pipe length		5 x DN
Outlet pipe length		1 x DN
Dimensions	[mm]	220 x 63.9 x 92.6
Materials	housing: stainless steel (316L/1.4404); Display: PFA; Sealing Display: FKM; connector: PBT	
Materials (wetted parts)	Pipe section: stainless steel (316L/1.4404)	
Nominal diameter	DN50 (2")	
Process connection	Clamp 2" DIN 32676 series C (ASME BPE)	
Process connection suitable for pipe standard	2" / Ø 50,8 mm x 1,65 mm (DIN 11866 series C); (DIN EN 10357 Series D)	
Surface characteristics Ra/Rz of the wetted parts	Ra < 0.4 µm	

Displays / operating elements

Display		colour display 1,44", 128 x 128 pixels
	Switching function	2 x LED, yellow
	diagnosis	1 x LED, three-colour

SUH400



Ultrasonic flow meter

SUC501JBFRKG/US


Remarks	
Remarks	MW = measured value
	MEW = Final value of the measuring range
	pulse and totaliser signal are only available for one of the two outputs
	the accuracy indications are adhered to over the entire application area
	the specified Ra surface characteristics of the wetted surfaces do not apply to the weld seam.
Pack quantity	1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection




1 (L+)	L+	
2 (OUT2)	MP2	DO2, AO, DI
3 (L-)	L-	
4 (OUT1)	MP1	DO1, FO, IO-Link

AO: analogue output; DI: digital input; DO: digital output; FO: frequency output; MP: multi-function connection

Diagrams and graphs

Note on pressure loss




SUH400

Ultrasonic flow meter

SUC501JBFRKG/US



derating ambient temperature



1 Ambient temperature

2 Medium temperature