




1 W DC- 4 GHz TNC/male COAXIAL TERMINATION

issue
09.jul.03

Page
1 / 1

DRAWING



General tolerances: +/- 0.5 mm

R F CHARACTERISTICS

FREQUENCY RANGE : DC - 4 GHz
 IMPEDANCE : 50 Ohms
 DC RESISTANCE : 50 Ohms ± 5 %
 V.S.W.R : DC - 1 GHz : ≤ 1.08
 1 - 4 GHz : ≤ 1.20
 PEAK POWER at 25°C (1µs,1%.) : 100 W
 AVERAGE POWER at 25°C : 1 W


MECHANICAL CHARACTERISTICS

CONNECTORS : TNC male per MIL-C 39012
 WEIGHT : < 16 g

ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE RANGE (°C) : -55 , +125
 STORAGE TEMPERATURE RANGE (°C) : -55 , +125

Power derating
Versus temperature



This information is given as an indication. In the continual goal to improve our products, we reserve the right to make any modifications judged necessary.

CREATION					
N° : 94105013					
PEN/EP: 94218					
Name: PG					
Date: 03. jan. 95	09.jul.03	Frequency range 2.5 GHz --> 4 GHz	AF	FG	
APP.: VE	ISSUE	REVISIONS	NAME	APPR.	

RADIALL®

101. rue P. Hoffmann - Z.I Ouest -
 93116 ROSNY/BOIS Cedex-FRANCE
 Phone: 33(1)49353535
 Fax : 33(1)48546363
 Tvx RADIA 235220F

4112-9212