

KEMET Part Number: PHE450RD6220JR06L2
(F450DY224J1K6C)

PHE450/F450, Film, Double Metallized Polypropylene, General Purpose, 0.22 uF, 5%, 1600 VDC, 85°C, Lead Spacing = 22.5mm



Dimensions

L	26mm MAX
H	24.5mm MAX
T	15.5mm MAX
S	22.5mm +/-0.4mm
LL	6mm -1mm
F	0.8mm +/-0.05mm
G	0.5mm NOM

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	176

General Information

Supplier:	KEMET
Series:	PHE450/F450
Dielectric:	Double Metallized Polypropylene
Style:	Radial
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	No
Miscellaneous:	The Rated Voltage Decreases 1.3%/C Between +85C And +105C. Rthja= 34 C/W (85C), 0.2 m/s

Specifications

Capacitance:	0.22 uF
Capacitance Tolerance:	5%
Voltage AC:	650 VAC
Voltage DC:	1600 VDC (85C), 1184 VDC (105C)
Temperature Range:	-55/+105°C
Rated Temperature:	85°C
Dissipation Factor:	0.03% 1kHz, 0.06% 10kHz
Insulation Resistance:	136.364 GOhms
Max dV/dt:	1800 V/us
Inductance:	6 nH