

M12 D-cod 4-pol an/- m/- Rail 1.0m



Image is for illustration purposes only. Please refer to product description.

Part number	09 48 800 0011 010
Specification	M12 D-cod 4-pol an/- m/- Rail 1.0m
HARTING eCatalogue	https://harting.com/09488000011010

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 D-coding
	Male Angled
	Overmoulded
Type of cable	Copper cable (round)
Description of the cable	for railway applications

Version

Cable length	1 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s
Limiting temperature	-40 ... +85 °C unmoved
	-25 ... +70 °C moved
Cable diameter	6.6 mm ± 0.2 mm
Minimum bending radius	6x Cable diameter (repeated bending)
	5x Cable diameter (singular bending)



Pushing Performance
Since 1945

Technical characteristics

Impedance 100 $\Omega \pm 5 \%$

Material properties

Material (cable)	Elastomer
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	760691ac-b4d2-427c-9996-5886190b813b
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	EN 45545-2
----------------	------------

Commercial data

Packaging size	2
Net weight	102.4 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140067738
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600