



## fitted with

work equipment  
connected load  
power consumption  
system of protection  
class of protection  
technology  
usage  
luminaire body  
lamp cover  
tubular sections  
balance of articulation joints  
weight (net)  
mains lead

fastening  
lens; dimensions  
lens; diopters  
add-on lens; dimensions

1 x circular fluorescent lamp T29-R 22W/840 G10q  
light colour neutral white  
Energy efficiency category A  
conventional ballast  
230 V/ 50 Hz  
approx. 31 W  
IP 20  
II  
switchable  
switch  
plastic, light grey  
polycarbonate, white opal  
plastic, light grey  
spring  
approx. 3.1 kg  
approx. 2.9 m; mains plug  
CEE 7/XVI  
table clamp (accessory), wall bracket (accessory)  
Ø 120 mm  
4  
not available



CEE 7/XVI

## illuminance

Comment: d=15cm

Em: 2112 lx

Emin: 850 lx

