



## high-performance backing pad with clamping nut dia. 125 H- GT125 M14 for angle grinders 125

high-performance backing pad with clamping nut dia. 125  
H-GT125 M14 for angle grinders 125

Item number: [44890090](#)

EAN: [4007220668122](#)

High-performance backing pad with a long tool life thanks to abrasion-resistant, glass-fibre-reinforced plastic. Impresses with particularly cool grinding due to radially arranged cooling fins, and high fibre-disc stock removal rate due to sturdy, rigid design.

### Technical information

|                               |                                   |
|-------------------------------|-----------------------------------|
| Dia. thread                   | M14                               |
| Max. RPM                      | 12200 RPM                         |
| PFERD TOOLS<br>type           | H-GT 125                          |
| Suitable for                  | Angle grinder<br>125, spindle M14 |
| Suitable for<br>diameter [mm] | 125                               |
| Version                       | No information                    |

### Recommendations for use

- ✔ Use fibre disc in accordance with ISO 15636 with backing pad on commercially available angle grinders.

### Ordering notes

- ✔ The matching clamping nut is included.

## Safety notes

- ✓ The maximum permitted peripheral speed is 80 m/s.
- ✓ For safety reasons, the maximum permitted rotational speed indicated must never be exceeded.

---

## Drive types

- ✓ Angle grinder
  - ✓ Cordless angle grinder
- 



August Rüggeberg GmbH & Co. KG  
Hauptstraße 13  
51709 Marienheide

+49 2264 9-0

+49 2264 9-400

[info@pferd.com](mailto:info@pferd.com)