



MINI-MATCH

TE Internal #: 1-5164713-1  
PCB Mount Header, Vertical, Board-to-Board, 11 Position, 2.5 mm [.098 in] Centerline, Unshrouded, Tin (Sn), Through Hole - Solder, Power & Signal  
[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**  
PCB Mount Orientation: **Vertical**  
Connector System: **Board-to-Board**  
Number of Positions: **11**  
Centerline (Pitch): **2.5 mm [.098 in]**

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Unshrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	11
PCB Mount Orientation	Vertical
Number of Positions	11

Body Features

Primary Product Color	Green
-----------------------	-------

Contact Features

Contact Mating Area Plating Material Thickness	3.04 μm[120 μin]
Mating Tab Width	2.79 mm[.11 in]
Contact Layout	Inline
Contact Base Material	Phosphor Bronze
Mating Tab Thickness	.5 mm[.02 in]





Contact Mating Area Plating Material	Tin (Sn)
Contact Type	Tab
Contact Current Rating (Max)	7 A

Termination Features

Rectangular Termination Post & Tail Width	.78 mm[.03 in]
Rectangular Termination Post & Tail Thickness	.5 mm[.02 in]
Termination Post & Tail Length	3.2 mm[.125 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	Without

Housing Features

Housing Material	PBT GF20
Centerline (Pitch)	2.5 mm[.098 in]

Dimensions

Connector Width	6.3 mm[.248 in]
PCB Thickness (Recommended)	1.6 mm[.06 in]
Connector Height	5.9 mm[.232 in]
Connector Length	27.5 mm[1.083 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	1500
--------------------	------





Packaging Method	Box
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought







TE Part #284697-E  
SRCP 1,27 4 M 1 SMD 137 E1 094 \* GU-H \*



TE Part #6-1625890-4  
2W SM M/OX 5% 680R



TE Part #ANT-LPC-FPC-100  
Antenna Vert 5G LTE FPC 100



TE Part #1-5164711-6  
16pos.MINI-MATCH FBTB, 2.5mm pitch



TE Part #1565994-4  
RITS HDR ASSY R/A SMT TYPE 4P WITH BOSS



TE Part #1462042-9  
IMC06CGR=IM Relay 140mW 12V 1CO




TE Part #5161500-7  
minimatch 7 pos male



TE Part #284695-E  
SRCP 1,27 2 M 1 SMD 137 E1 094 \* GU-H \*



TE Part #826947-4  
4P MOD2 STIFT LEI



TE Part #9-329631-3  
JAM NUT

Documents

Product Drawings  
11P.MINI-MATCH ASSY

English

CAD Files  
Customer View Model  
ENG\_CVM\_1-5164713-1\_A.3d\_igs.zip

English

Customer View Model  
ENG\_CVM\_1-5164713-1\_A.3d\_stp.zip

English

Customer View Model  
ENG\_CVM\_1-5164713-1\_A.2d\_dxf.zip

English

3D PDF

English

Product Specifications





Product Specification

Mini Match Connection System

English

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

German