


FEATURES

- **High thermal conductivity of 1.6 W/mK:** Ensures efficient heat transfer, reducing the risk of overheating.
- **Wide operating temperature range (-60°C to 240°C):** Suitable for various environments, maintaining performance under extreme conditions.
- **Non-adhesive design:** Allows for easy repositioning and reuse, providing flexibility in application.
- **Compact dimensions (12.7 mm length, 19 mm width, 0.25 mm thickness):** Fits into tight spaces without compromising on performance.
- **Brick red colour:** Easily identifiable for quick installation and maintenance.

RS PRO 1.6 W/mK Thermal Conductive Pad, 240°C Max Temperature

RS Stock No: 625-759



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO thermal conductive pad is designed to efficiently transfer heat between components, ensuring optimal performance and longevity of electronic devices. With a high thermal conductivity of 1.6 W/mK, it is ideal for applications requiring effective heat dissipation.

General Specifications

Colour	Brick Red
Product Type	Thermal Conductive Pad
Self-Adhesive	No

Mechanical Specifications

Length	12.7 mm
Thickness	0.25 mm
Width	19 mm

Operation Environment Specifications

Maximum Operating Temperature	240 °C
Minimum Operating Temperature	-60 °C

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, REACH, RoHS
---------------------	-----------------------------------

Thermal Performance Specifications

Thermal Conductivity	1.6 W/mK
----------------------	----------