



4549 - 4550 - 4551 Torque wrench TORCOFIX K 1-850 N·m / 0.75-630 lbf·ft

Use:

- Controlled screw tightening in the most widely used range of 1 - 850 N·m / 0.75 - 630 lbf·ft (guide for screws M3-6.9 to M24-8.8, M30-5.6)
- Adjustable, releasing and sturdy tubular torque wrench with integrated ratchet and with square drive for industry and the trades

Features:

- Classified to DIN EN ISO 6789:2003 Type II Class A, with a factory certificate. Working accuracy: +/- 3 % tolerance of scale set torque. The specification of the standard (+/- 4 %) is exceeded.
- For controlled bi-directional tightening
- 1/4", 3/8", 1/2" interchangeable mushroom head with ball locking device. As from 3/4" with push through square drive with pin-locking mechanism
- Sturdy, satin chrome-plated tubular steel construction, with chrome-plated ratchet head and top-grade plastic parts
- Ergonomically shaped, convenient black plastic handgrip with calibration aid
- Dual scale N·m and lbf·ft below a window with a magnifying-glass effect
- With micrometre scale for main N·m scale for setting interim values
- Release system triggers a tactile and audible signal
- Ergonomic system for torque adjustment



□"	■	N·m	lbf·ft	🔧	scale ring	lw	a	b	c	d	🔧	Code	No.
1/4	6.3	1-5	0,75-3,7	0,25 N·m	0,025 N·m	146.0	25.3	35	26	224.0	0.323	2201429	4549-00
1/4	6.3	2-25	1,5-18	1 N·m	0,1 N·m	206.5	24.0	35	26	284.5	0.450	1545132	4549-02
3/8	10.0	5-50	3,5-37	2,5 N·m	0,25 N·m	256.5	24.0	35	26	334.5	0.540	1545140	4549-05
1/2	12.5	10-100	8-75	5 N·m	0,5 N·m	303.5	33.0	44	35	394.0	0.900	7601530	4550-10
1/2	12.5	20-200	15-150	10 N·m	1 N·m	394.5	33.0	44	35	485.0	1.100	7601610	4550-20
3/4	20.0	250-850	185-630	10 N·m	1 N·m	1,276.0	31.0	69	1276	1,379.0	4.700	1950525	4551-85