

Datasheet

Adjustable Elastic Wrist Strap, 4mm

RS-798-9288



Wrist Band



Coiled Cord



Meets the requirements of EN 61340-5-1 tested per ANSI/ESD S1.1 and IEC 61340-5-1 Clause A.1

Wrist Band

- No metal to skin contact
- Choice for those with skin allergies
- Widely adjustable, elasticated fabric band
- Conductive fibres on the inside
- Vermason logo molded into the cap
- Designed to be used with a Coiled Cord with a one megohm current limiting resistor meeting the EN 61340-5-1 Personnel Grounding requirements tested per ANSI/ESD S1.1.
- R_S interior of band: $< 1 \times 10^5$ ohms Test Method: ANSI/ESD S1.1 (5.2)
- R_S exterior of band: $> 1 \times 10^7$ ohms Test Method: ANSI/ESD S1.1 (5.2)
- Circumference: Adjustable from 120mm to 200mm
- Colour: Dark Blue
- Termination: 4mm stud
- Weight: 8g

Cord

- 2.5mm polyurethane insulation
- Conductor is high strength 7-end duplex tinsel for strength and flexibility
- Dielectric Strength: Cords withstand 1250 volts DC for at least one minute
- Standard cords are marked and date coded
- Length: 2m
- Colour: yellow
- Terminations: 10mm and 4mm socket
- 1 megohm \pm 20% current limiting resistor built in each socket

Unless otherwise noted, tolerance \pm 10%

Specifications and procedures subject to change without notice.