

EVO-STIK MULTI-PURPOSE SILICONE SEALANT WHITE
Supersedes Date: 10-Oct-2018

Revision Date 18-Oct-2018
Revision Number 1.01

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product Identifier

Product Name EVO-STIK MULTI-PURPOSE SILICONE SEALANT WHITE
Pure substance/mixture Mixture

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended use Sealant.
Uses advised against None known

1.3. Details of the supplier of the safety data sheet

E-mail address SDS.box-EU@bostik.com

1.4. Emergency telephone number

United Kingdom +44 (1785) 272650
Ireland +353 (1) 8624900 (Monday- Friday 9am-5pm)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Regulation (EC) No 1272/2008

Not classified

2.2. Label Elements

Not classified

Signal word
None

Hazard statements
Not classified

EU Specific Hazard Statements

EUH208 - Contains 3(2H)-Isothiazolone, 4,5-dichloro-2-octyl-. May produce an allergic reaction
EUH210 - Safety data sheet available on request

Precautionary statements

P101 - If medical advice is needed, have product container or label at hand
P102 - Keep out of reach of children

2.3. Other Hazards

No information available

PBT and vPvB assessment

The components in this formulation do not meet the criteria for classification as PBT or vPvB

SECTION 3: Composition/information on ingredients

Safety Data Sheet

EVO-STIK MULTI-PURPOSE SILICONE SEALANT WHITE
Supersedes Date: 10-Oct-2018

Revision Date 18-Oct-2018
Revision Number 1.01

3.1 Substances

Not applicable

3.2 Mixtures

Chemical Name	EC No.	CAS No.	Weight-%	Classification according to Regulation (EC) No. 1272/2008 [CLP]	Specific concentration limit (SCL)	REACH Registration Number
Hydrocarbons, C13-C23, n-alkanes, isoalkanes, cyclics, < 0.03% aromatics	932-078-5	--	>25 - <40	Asp. Tox. 1 (H304)		01-2119552497-29-xxxx
Triacetoxyp(ropyl)silane	241-816-9	17865-07-5	1 - <3	Skin Corr. 1B (H314)		01-2119966899-07-XXXX
Silanetriol, methyl-, triacetate	224-221-9	4253-34-3	1 - <3	Skin Corr. 1C (H314) Acute Tox. 4 (H302) (EUH014)		01-2119962266-32-XXXX
3(2H)-Isothiazolone, 4,5-dichloro-2-octyl-	264-843-8	64359-81-5	0.01 - <0.1	Skin Corr. 1B (H314) Eye Dam. 1 (H318) Skin Sens. 1A (H317) Acute Tox. 4 (H302) Acute Tox. 2 (H330) Aquatic Acute 1 (H400) Aquatic Chronic 1 (410)		No data available

Full text of H- and EUH-phrases: see section 16

Note: ^ indicates not classified, however, the substance is listed in section 3 as it has an OEL

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (Regulation (EC) No. 1907/2006 (REACH), Article 59)

SECTION 4: First aid measures

4.1. Description of first aid measures

General advice	Show this safety data sheet to the doctor in attendance. If irritation persists or eye and/or skin remains bonded: Get medical advice/attention.
Inhalation	Remove to fresh air. IF exposed or concerned: Get medical advice/attention.
Eye contact	If eyelids are bonded closed or if skin to skin or skin to clothing bonding has occurred, release bonding by covering affected area with a pad wetted with warm water. Do not force eyes or any bonded skin apart. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If irritation persists or eye and/or skin remains bonded: Get medical advice/attention.
Skin contact	If eyelids are bonded closed or if skin to skin or skin to clothing bonding has occurred,

Safety Data Sheet

EVO-STIK MULTI-PURPOSE SILICONE SEALANT WHITE
Supersedes Date: 10-Oct-2018

Revision Date 18-Oct-2018
Revision Number 1.01

release bonding by covering affected area with a pad wetted with warm water. Do not force eyes or any bonded skin apart. If irritation persists or eye and/or skin remains bonded: Get medical advice/attention.

Ingestion Clean mouth with water. Do NOT induce vomiting. Drink 1 or 2 glasses of water. Never give anything by mouth to an unconscious person.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms No information available.

4.3. Indication of any immediate medical attention and special treatment needed

Note to doctors Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media Full water jet. Do not scatter spilled material with high pressure water streams.

5.2. Special hazards arising from the substance or mixture

Specific hazards arising from the chemical Bonds skin and eyes in seconds.

5.3. Advice for firefighters

Special protective equipment for fire-fighters Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Avoid contact with skin, eyes or clothing. Ensure adequate ventilation. Use personal protective equipment as required. See section 8 for more information.

Other information Ventilate the area. Prevent further leakage or spillage if safe to do so.

For emergency responders Use personal protection recommended in Section 8.

6.2. Environmental precautions

Environmental precautions Do not flush into surface water or sanitary sewer system. Do not allow to enter into soil/subsoil. See Section 12 for additional Ecological Information.

6.3. Methods and material for containment and cleaning up

Methods for containment Use a non-combustible material like vermiculite, sand or earth to soak up the product and place into a container for later disposal.

Methods for cleaning up Take up mechanically, placing in appropriate containers for disposal.

6.4. Reference to other sections

Reference to other sections See section 8 for more information. See section 13 for more information.

Safety Data Sheet

EVO-STIK MULTI-PURPOSE SILICONE SEALANT WHITE
Supersedes Date: 10-Oct-2018

Revision Date 18-Oct-2018
Revision Number 1.01

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Use personal protection equipment. Do not eat, drink or smoke when using this product. See section 8 for more information.

General hygiene considerations Handle in accordance with good industrial hygiene and safety practice. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Take off all contaminated clothing and wash it before reuse.

7.2. Conditions for safe storage, including any incompatibilities

Storage Conditions Keep container tightly closed in a dry and well-ventilated place. Keep away from food, drink and animal feedingstuffs.

7.3. Specific end use(s)

Specific Use(s)
Sealant.

Risk Management Methods (RMM) The information required is contained in this Safety Data Sheet.

Other Information Observe technical data sheet.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Exposure Limits This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies

Derived No Effect Level (DNEL) No information available

Predicted No Effect Concentration (PNEC) No information available.

8.2. Exposure controls

Engineering Controls Ensure adequate ventilation, especially in confined areas.

Personal Protective Equipment

Eye/Face Protection Tight sealing safety goggles.
Skin and Body Protection Suitable protective clothing.

Environmental Exposure Controls No information available.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical State Paste / Gel
Appearance No information available
Colour White
Odour Acetic acid.
Odour Threshold No information available

Safety Data Sheet

EVO-STIK MULTI-PURPOSE SILICONE SEALANT WHITE
Supersedes Date: 10-Oct-2018

Revision Date 18-Oct-2018
Revision Number 1.01

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	No data available	
Melting point / freezing point	No data available	
Boiling point / boiling range	> 300 °C	
Flash Point	> 100 °C	
Evaporation Rate	No data available	
Flammability (solid, gas)	No data available	
Flammability Limit in Air		
Upper flammability or explosive limits	No data available	
Lower flammability or explosive limits	No data available	
Vapour Pressure	No data available	
Vapour Density	No data available	
Relative Density	No data available	
Water Solubility	Immiscible in water	
Solubility(ies)	No data available	
Partition coefficient	No data available	
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Kinematic Viscosity	No data available	
Dynamic Viscosity	No data available	
Explosive properties	No data available	
Oxidising properties	No data available	

9.2. Other information

Solid content (%)	No information available
Softening Point	No information available
Molecular Weight	No information available
VOC (volatile organic compound)	No information available
Density	0.97 g/cm ³
Bulk Density	No information available

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity No information available.

10.2. Chemical stability

Stability Stable under normal conditions.

Explosion Data

Sensitivity to mechanical impact None.

Sensitivity to static discharge None.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions None under normal processing.

10.4. Conditions to avoid

Conditions to avoid None known based on information supplied.

10.5. Incompatible materials

Incompatible materials None known based on information supplied.

10.6. Hazardous decomposition products

Safety Data Sheet

EVO-STIK MULTI-PURPOSE SILICONE SEALANT WHITE
Supersedes Date: 10-Oct-2018

Revision Date 18-Oct-2018
Revision Number 1.01

Hazardous decomposition products None under normal use conditions. Stable under recommended storage conditions.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Information on likely routes of exposure

Product information

Inhalation Based on available data, the classification criteria are not met.
Eye contact Bonds skin and eyes in seconds.
Skin contact Bonds skin and eyes in seconds.
Ingestion Based on available data, the classification criteria are not met.

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms No information available.

Numerical measures of toxicity

Acute Toxicity

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral) 64,000.00

Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Hydrocarbons, C13-C23, n-alkanes, isoalkanes, cyclics, < 0.03% aromatics --	LD50 > 5000 mg/kg (rat) OECD 401	LD50 > 2000 mg/kg (rabbit) OECD 402	
Silanetriol, methyl-, triacetate 4253-34-3	LD50 = 1600 mg/kg (Rat) OECD 401		

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation Based on available data, the classification criteria are not met.
Serious eye damage/eye irritation Based on available data, the classification criteria are not met.
Respiratory or skin sensitisation Based on available data, the classification criteria are not met.
Germ cell mutagenicity Based on available data, the classification criteria are not met.
Carcinogenicity Based on available data, the classification criteria are not met.
Reproductive toxicity Based on available data, the classification criteria are not met.
STOT - single exposure Based on available data, the classification criteria are not met.
STOT - repeated exposure Based on available data, the classification criteria are not met.

Safety Data Sheet

EVO-STIK MULTI-PURPOSE SILICONE SEALANT WHITE
Supersedes Date: 10-Oct-2018

Revision Date 18-Oct-2018
Revision Number 1.01

Aspiration hazard Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

12.1. Toxicity

Ecotoxicity

Chemical Name	Algae/aquatic plants	Fish	Toxicity to Micro-organisms	Crustacea	M-Factor
Hydrocarbons, C13-C23, n-alkanes, isoalkanes, cyclics, < 0.03% aromatics --	EL50 (72h) > 10 000 mg/L (Skeletonema costatum)	LL50 (96h) > 1028 mg/L (Scophthalmus maximus)	-	LL50 (48h) > > 3193 mg/l (Acartia tonsa)	-
3(2H)-Isothiazolone, 4,5-dichloro-2-octyl-64359-81-5	EC50 (72h) =0.025 mg/L Algae (Scenedesmus subspicatus)(OEC D 201)	LC50 (96h) 0.0078 mg/L Fish (Oncorhynchus mykiss)(OECD 203)	-	EC50 (48h) 0.0097 mg/L Daphnia magna (OECD 202)	-

12.2. Persistence and degradability

Persistence and degradability No information available.

12.3. Bioaccumulative potential

Bioaccumulative potential There is no data for this product.

Component Information

Chemical Name	Partition coefficient
3(2H)-Isothiazolone, 4,5-dichloro-2-octyl-64359-81-5	4.4

12.4. Mobility in soil

Mobility in soil No information available.

12.5. Results of PBT and vPvB assessment

PBT and vPvB assessment . The components in this formulation do not meet the criteria for classification as PBT or vPvB.

Chemical Name	PBT and vPvB assessment
Triacetoxyp(ropyl)silane 17865-07-5	The substance is not PBT / vPvB
Silanetriol, methyl-, triacetate 4253-34-3	The substance is not PBT / vPvB

12.6. Other adverse effects

Other Adverse Effects No information available.

SECTION 13: Disposal considerations

Safety Data Sheet

EVO-STIK MULTI-PURPOSE SILICONE SEALANT WHITE
Supersedes Date: 10-Oct-2018

Revision Date 18-Oct-2018
Revision Number 1.01

13.1. Waste treatment methods

Waste from residues/unused products	Dispose of contents/container in accordance with local, regional, national, and international regulations as applicable.
Contaminated packaging	Do not reuse empty containers. Handle contaminated packages in the same way as the product itself.
European Waste Catalogue	08 04 09* waste adhesives and sealants containing organic solvents or other dangerous substances
Other Information	Waste codes should be assigned by the user based on the application for which the product was used.

SECTION 14: Transport information

Land transport (ADR/RID)

14.1 UN Number	Not regulated
14.2 Proper Shipping Name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing Group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special Provisions	None

IMDG

14.1 UN Number	Not regulated
14.2 Proper Shipping Name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing Group	Not regulated
14.5 Marine Pollutant	Np
14.6 Special Provisions	None
14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	No information available

Air transport (ICAO-TI / IATA-DGR)

14.1 UN Number	Not regulated
14.2 Proper Shipping Name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing Group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special Provisions	None

Section 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

European Union

Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work

Check whether measures in accordance with Directive 94/33/EC for the protection of young people at work must be taken.

Take note of Directive 92/85/EC on the protection of pregnant and breastfeeding women at work

Registration, Evaluation, Authorization, and Restriction of Chemicals (REACH) Regulation (EC 1907/2006)

EU-REACH (1907/2006) - Candidate List of Substances of Very High Concern (SVHC) for Authorization in accordance with Article 59

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (Regulation (EC) No.

Safety Data Sheet

EVO-STIK MULTI-PURPOSE SILICONE SEALANT WHITE
Supersedes Date: 10-Oct-2018

Revision Date 18-Oct-2018
Revision Number 1.01

1907/2006 (REACH), Article 59)

EU-REACH (1907/2006) - Annex XVII - Substances subject to Restriction

This product does not contain substances subject to restriction (Regulation (EC) No. 1907/2006 (REACH), Annex XVII).

EU-REACH (1907/2006) - Annex XIV - List of substances subject to Authorization

This product does not contain substances subject to authorisation (Regulation (EC) No. 1907/2006 (REACH), Annex XIV)

Ozone-depleting substances (ODS) regulation (EC) 1005/2009

Not applicable

Persistent Organic Pollutants

Not applicable

15.2. Chemical safety assessment

Chemical Safety Assessments have been carried out by the Reach registrants for substances registered at >10 tpa. No Chemical Safety Assessment has been carried out for this mixture

SECTION 16: Other information

Key or legend to abbreviations and acronyms used in the safety data sheet

Legend

SVHC: Substances of Very High Concern for Authorisation:

Legend SECTION 8: Exposure controls/personal protection

TWA TWA (time-weighted average)

STEL

STEL (Short Term Exposure Limit)

Ceiling Maximum limit value

*

Skin designation

PBT Persistent, Bioaccumulative, and Toxic (PBT) Chemicals

STOT RE Specific target organ toxicity - Repeated exposure

STOT SE Specific target organ toxicity - Single exposure

EWC: European Waste Catalogue

Key literature references and sources for data

Classification and labeling data calculated from data received from raw material suppliers

Prepared By Product Safety & Regulatory Affairs

Revision Date 18-Oct-2018

Indication of changes

Revision Note SDS sections updated: 2, 3, 11.

Training Advice No information available

Further information No information available

This material safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of

Safety Data Sheet

EVO-STIK MULTI-PURPOSE SILICONE SEALANT WHITE
Supersedes Date: 10-Oct-2018

Revision Date 18-Oct-2018
Revision Number 1.01

its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet