



Insulation monitoring relays, 0 - 690 V AC, 0 - 1000 V DC

Part no. **EMR6-RC690**
 Catalog No. **184775**
 Eaton Catalog No. **EMR6-RC690**

Technical data

General

Standards			IEC/EN 60255-6,
Lifespan, mechanical	Operations	x 10 ⁶	30
Climatic proofing			Damp heat, cyclical to IEC 60068-2-30: 24 h cycle, 55° C, 93% relative humidity, 96 h
Ambient temperature			
Operation		°C	
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	+ 60
Storage		°C	- 40 - 85
Mounting position			As required
Shock resistance			Class 2
Degree of protection			
Terminals			IP20
Enclosures			IP50
Terminal capacities		mm ²	
Solid		mm ²	1 x 0.5-2.5 (1 x 18-14 AWG)
Flexible with ferrule		mm ²	2 x 0.5-1.5 (2 x 18-16 AWG)
Standard screwdriver		mm	5.5 x 0.8
Tightening torque		Nm	0.5 - 0.8
Fixing			Snap fixing, top-hat rail IEC/EN 60715

Contacts

Rated impulse withstand voltage	U _{imp}	V AC	4000
Overvoltage category/pollution degree			III/3

Power supply

Voltage tolerance		x U _c	0.85 - 1.1
Rated frequency	f	Hz	50 - 60
Duty factor		% DF	100

Measuring circuits

Cable length for cancellation- and test button		m	10
--	--	---	----

Status indication

Supply voltage			LED, green
Fault at L+			LED, red
Fault at L-			LED, red

Relay output contacts

Rated operational current	I _e	A	
AC-12 at 230 V	I _e	A	5
AC-15 with 230 V	I _e	A	3
DC-13 at 24 V	I _e	A	2.5
Lifespan, electrical (AC-12/230 V/4 A)	Operations	x 10 ⁶	
Lifespan, electrical	Operations	x 10 ⁶	0.1
Short-circuit rating			
max. fuse	Fast/gL	A	5

Electromagnetic compatibility (EMC)

Electromagnetic compatibility			IEC/EN 60947-6-2
ESD	Air/contact discharge	kV	IEC/EN 61000-4-2 level 3

HF-immunity to radiation		IEC/EN 61000-4-3 level 3
Burst		IEC/EN 61000-4-4 level 3
Surge		IEC/EN 61000-4-5 Level 4
HF-immunity to line-conducted interference		IEC/EN 61000-4-6 level 3


Design verification as per IEC/EN 61439

Technical data for design verification		
Operating ambient temperature min.	°C	-25
Operating ambient temperature max.	°C	60


Technical data ETIM 7.0

Relays (EG000019) / Insulation and earth fault monitoring relay (EC001444)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Monitoring equipment (low-voltage switch technology) / Insulation-/earth connection monitoring equipment (ecl@ss10.0.1-27-37-18-07 [AKF101014])		
Type of electric connection		Screw connection
Rated control supply voltage Us at AC 50HZ	V	0 - 0
Rated control supply voltage Us at AC 60HZ	V	0 - 0
Rated control supply voltage Us at DC	V	0 - 0
Voltage type for actuating		AC/DC
With detachable clamps		No
Function		For mixed system
Rated voltage	V	0 - 690
Rated frequency	Hz	15 - 400
Line capacity	µF	20
Response value impedance 1	kOhm	1 - 100
Response value impedance 2	kOhm	1 - 200
Indication of insulation value		No
Error registration possible		No
Number of contacts as normally closed contact		0
Number of contacts as normally open contact		0
Number of contacts as change-over contact		0
Width	mm	45
Height	mm	85
Depth	mm	110


Characteristics




AC load (resistive)



DC load (resistive)



Derating factor F with inductive AC load



Dimensions

