



Main

Device short name	ITA 1c
Product or component type	Yearly programmable time switch
Number of channels	1
Battery type	Lithium
Function available	Pulse programming External input for override Automatic winter/summer time changeover Time synchronisation via antenna possible Manual or software programming Cycle programming
Type of setting	Absence for holidays function PIN code
Language	Danish Dutch English Finnish French German Hungarian Italian Norwegian Polish Portuguese Romanian Spanish Swedish Czech

Complementary

Device application	Building
Cycle duration	24 hours + 7 days + year
Maximum number of switchings	300
Minimum interval duration	1 min
Accuracy	+/- 0.5 s/day 20 °C
Power consumption	1.4...1.9 W
Maximum switching current	6 A - 250 V AC pf = 0.6 16 A - 250 V AC pf = 1
[Ue] rated operational voltage	230 V AC 50/60 Hz
Display type	Backlit LCD
Battery life	10 yr
Backup time	10 years time and program saving
Mounting support	DIN rail
9 mm pitches	4
Colour tint	White (RAL 9003)
Connections - terminals	Screw terminals
Width	35.8 mm
Height	90 mm
Depth	63 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient air temperature for operation	-30...55 °C
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1426 - Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - go to CaP for more details
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Available Download End Of Life Manual