



3MN6



Actual product appearance may vary.

MN Series Basic Switch, Double Pole Double Throw Double Break Circuitry, 15 A at 480 Vac, Pin Plunger Actuator, 1,95 N - 3,1 N [7 oz - 11 oz] Operating Force, Quick Connect Termination, Fine Silver Contacts, Screw Termination, CSA, UL

Features

- Double-break circuitry
- Power load switching capability to 15 A at 600 Vac
- Motor handling capacity of 746 W [1 hp] at 240 Vac
- Long mechanical life to 10,000,000 cycles at 95% survival
- Space between terminals reduces possibility of shorting
- Arc-resistant plastic

Potential Applications

- Machine Tools
- Presses
- Industrial equipment

Description

MICRO SWITCH™ 3MN Series double-break standard basic switches provide easy gang mounting.

Product Specifications	
Switch Type	Standard 25,4 mm H x 17,8 mm W x 50,8 mm L [1.0 in H x 0.7 in W x 2.0 in L]
Sealed	No
Ampere Rating	15 A
Circuitry	Two Circuit, Double Break (2 CKT DB)
Actuator	Pin Plunger
Termination	Screw
Operating Temperature Range	-55 °C to 85 °C [-67 °F to 185 °F]
Voltage	480 Vac
Approvals	CSA,UL
Contact Type	Fine Silver
Operating Force (O.F.)	1,95 N - 3,1 N [7.0 oz - 11.0 oz]
Release Force (R.F.)	1,11 N [4.0 oz] min.
Pretravel (P.T.)	1,52 mm [0.060 in] max.

Overtravel (O.T.)	2.03 mm [0.080 in] min.
Differential Travel (D.T.)	0,38 mm - 0,63 mm [0.015 in - 0.025 in]
Operating Position (O.P.)	2,16 mm [0.085 in] max.
Material	Plastic
Housing Material	General Purpose Phenolic
Agency Approvals and Standards	1054
Mounting Centers	54,1 mm [2.13 in]
Weight	34,5 g [0.076 lb]
Package Height	30,5 mm [1.2 in]
Package Width	17,3 mm [0.68 in]
Package Length	63,5 mm [2.50 in]
Recommended For	Lower force
Availability	Global
UNSPSC Code	30211905
UNSPSC Commodity	30211905 Snap switches
Series Name	MN

MICRO SWITCH



A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
PINEPORT, ILLINOIS

FED. MFR. CODE 91929

SWITCH - BASIC


CATALOG LISTING

3MN6



NOTE-

1- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON $2.125 \pm .005$ CENTERS



CIRCUIT DIAGRAM

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE ——— 7-11 OZ

RELEASE FORCE ——— 4 OZ MIN

DIFFERENTIAL TRAVEL ——— .015-.025

OVERTRAVEL ——— .080 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
SEE CIRCUIT DIAGRAM

UL RECOGNIZED - FILE E22779

15 A-120, 240, 480, OR 600 VAC

1/2 HP-120 VAC; 1 HP-240 VAC

0.8 A-115 VDC; 0.4 A-230 VDC

PILOT DUTY RATING: 600 VAC MAX

(C)



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) $\pm .030$

TWO PLACE (.00) $\pm .015$

THREE PLACE (.000) $\pm .005$

ANGLES $\pm$

WEIGHT

3MN6

M

DRAWING
NUMBER

2

X

5

ISSUE

3

REPLACES

RELEASE NO. SR 8314

CHECK

REVISIONS

A SR 8314
M B F
24 JUNE 59

B CORR
L M H
AUG 59

C CO 15776
K L B
APR 61

D CO 39150
W L W
6 SEPT 77

CHECK

9 APR 59

24 JUN 59

6 CH

59

CHECK

9 APR

59

R. E. R.