




Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**

Insertion & Extraction Tool Application: **Contact-to-Wire**

## Features

### Product Type Features

Insertion & Extraction Tool Type	Contact Extraction
Insertion & Extraction Tool Application	Contact-to-Wire

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 6-928918-6  
MQS PIN CONT



TE Part # 6-962885-6  
MQS BUCHS-KONT EDS



TE Part # 5-963729-6  
MQS SOCKET CONTACT



TE Part # 2-963725-1  
MQS PIN CONTACT



TE Part # 1-2298627-1  
24POS, HYBRID, TAB HSG ASSY,  
UNSLD, COD A



TE Part # 2298566-1  
22POSN., TAB ASSY, MCON1.2, MQS,  
MCP2.8



TE Part # 2294218-1  
4POS MQS REC COD A




TE Part # 2298622-1  
24POS, HYBRID, REC HSG ASSY,  
UNSLD, COD A



TE Part # 1740335-4  
MICRO QUADLOK SYSTEM PIN  
CONTACT



TE Part # 2322948-2  
6POS, MQS, REC HSG, UNSLD



TE Part # 6-963715-6  
MQS REC CONT



TE Part # 6-963716-1  
MQS0,63 Sn tab LL unseal. 0,5-0,75




TE Part # 963728-2  
MQS PIN CONTACT SWS



TE Part # 965909-1  
MQS PIN CONTACT SWS



TE Part # 929399-1  
SOCKET CONTACT 0.63X1.2



TE Part # 5-1394702-3  
MQS 2P 0.63, TERMINAL, AG, LL 0.25-  
0.35



TE Part # 6-144969-1  
MQS RECEPTACLE



TE Part # 6-1452013-1  
MQS BU-KONTAKT



TE Part # 1355720-1  
MQS PIN CONTACT (LP)



TE Part # 2-963728-2  
LP MQS PIN EDS SANTOVAC

## Also in the Series | NECTOR S



Insertion & Extraction Tools(3)



Plug & Socket Lighting Connector  
Accessories(38)



Plug & Socket Lighting Connectors(30)



Power Terminals(4)

## Customers Also Bought



TE Part #K1160758  
Plunger Switch 44-01-069




TE Part #K1154427  
Battery Disconnecter 35-524-241-R-900



TE Part #K1152919  
Limit switch G12-421-M-18



TE Part #CAT-T4827-CH8172  
Timer Connector Housing



TE Part #2-1658526-4  
609-5041LF FEM SOCKET,LEAD FREE



TE Part #2063530-1  
SDE MQS 0.5-0.75mm2 ASSY



TE Part #1-2378180-1  
7POS,HYBRID,HDR ASSY,180DEG,  
COD A



TE Part #5788794-1  
25 HTMSFL PLUG RA 318 (IN,BL)



TE Part #2318777-1  
RESOLVER,ROTOR WITHOUT RIVETS  
MARKED



## Documents

[Product Drawings](#)  
[EXTRACTION TOOL](#)

English

---

[Product Specifications](#)  
[Application Specification](#)

English