


Geberit Mapress T-piece, reduced



Example image

APPLICATION PURPOSES

- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For compressed air (oil purity class 0–3)
- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

TECHNICAL DATA

Product material Brass CW617N

Art. no.	DN	d, ø mm	d1, ø mm	d2, ø mm	arc °	L cm	L1 cm	I cm	I2 cm	Z cm	Z1 cm	Z2 cm
These articles are suitable for the following system: Geberit Mapress Therm												
61191	12 / 10 / 10	15	12	12	90	6.4	3.3	3.2	3.2	1.2	1.6	1.5
61192	15 / 12 / 12	18	15	15	90	7.4	3.5	3.4	4	1.4	1.5	2
61193	15 / 15 / 12	18	18	15	90	7.4	3.4	3.4	4	1.4	1.4	2
61194	20 / 12 / 12	22	15	15	90	7.7	3.8	3.4	4.3	1.3	1.8	2.3

Art.no.	DN	d, ø mm	d1, ø mm	d2, ø mm	arc °	L cm	L1 cm	I cm	l2 cm	z cm	z1 cm	z2 cm
61195	20 / 15 / 15	22	18	18	90	7.4	4	3.7	3.7	1.6	2	1.7
61196	20 / 20 / 12	22	22	15	90	8.3	3.7	3.7	4.6	1.6	1.6	2.6
61197	25 / 20 / 20	28	22	22	90	8	4.1	4.2	3.8	1.9	2	1.7
These articles are suitable for the following system: Geberit Mapress Carbon Steel												
61191	12 / 10 / 10	15	12	12	90	6.4	3.3	3.2	3.2	1.2	1.6	1.5
61192	15 / 12 / 12	18	15	15	90	7.4	3.5	3.4	4	1.4	1.5	2
61193	15 / 15 / 12	18	18	15	90	7.4	3.4	3.4	4	1.4	1.4	2
61194	20 / 12 / 12	22	15	15	90	7.7	3.8	3.4	4.3	1.3	1.8	2.3
61195	20 / 15 / 15	22	18	18	90	7.4	4	3.7	3.7	1.6	2	1.7
61196	20 / 20 / 12	22	22	15	90	8.3	3.7	3.7	4.6	1.6	1.6	2.6
61197	25 / 20 / 20	28	22	22	90	8	4.1	4.2	3.8	1.9	2	1.7