


29976BM-2-006 (Full Detent, PCB Board Edge Mount, SMPM-T male)

29976BM-2-006

Properties

- The SMPM-T is the smallest threaded interface available that complies with MIL-STD-348
- Threaded coupling mechanism improves control over the interface dimensions
- Applicable up to 65 GHz

**Product configuration**

Interface type	Gender	Standard
SMPM-T	plug	MIL-STD-348

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PTFE (Polytetrafluoroethylene)	

Electrical data

Impedance	50 Ω
Interface frequency	65 GHz

Mechanical data

Weight	0.41 g
Mating cycles	100
Board mounting type	edge mount
Number of printlegs	2
Height above PCB HA	2.11 mm

Environmental data

Operation temperature	-55 °C ... 125 °C
-----------------------	-------------------

Material compliance

Item number	Directive / Regulation	Rating	Exemptions / Details
80367075	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c

29976BM-2-006 (Full Detent, PCB Board Edge Mount, SMPM-T male)
29976BM-2-006

Ordering Information Table		
Item number	Item description	Packaging type
80367075	29976BM-2-006	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P51161 / Date of publication: 06.11.2025 / uncontrolled copy