Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



Plain door + lock syst. for Thalassa PHD enclosure - 107

Local distributor code:

403419159 NSYDPHD107P

EAN Code: 3606480841316

Main

Range	Thalassa	
Offer type	Spare part	
Accessory / separate part category	Enclosure accessory	
Product or component type	Door	
Application	Heavy duty	
For enclosure nominal dimensions	- H: 1093 mm W: 700 mm	
Mounting location	Front	
Range compatibility	Thalassa Thalassa PHD suitable enclosure	
Device composition	hinges lock door door retainer handle	
Quantity per set	Set of 1	

Complementary

Material	Polyester double reinforced with fibreglass	
Colour	Grey (RAL 7035)	
Key number	1242 E	
Door type	Plain	
Door opening side	Reversible (120 °)	

Environment

IK degree of protection	IK10 conforming to IEC 62262
Environmental characteristic	Fire resistance conforming to EN 1794-2: 2011

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.000 cm
Package 1 Width	79.000 cm
Package 1 Length	100.000 cm
Package 1 Weight	7.980 kg

Logistical informations

Country of origin

ES

Contractual warranty

Warranty

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	1341ad4e-77b9-40e3-bab0-32043fbc5959
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No