

GSB 18 V-21 Professional Combi



Durable all-rounder from the 18 V class, in a compact format



Specification	
Torque max (hard/soft)	55 / 21 Nm
No-load speed (1 st gear / 2 nd gear)	0-480/0-1800 rpm
Chuck capacity	13 mm
Max drilling wood	35 mm
Max drilling steel	10 mm
Max drilling masonry	10 mm
LED light	Yes
Torque settings	20+1
Part Number:	0.615.990.M00

Key Product Features	Consumer Benefit
Compact and Ergonomic Design	Increasing handling and comfort
Electronic Motor Protection	protects the motor against overload and ensures a long lifetime
Electronic Cell Protection	protects the battery against overload, overheating and deep discharge therefore protecting it against irreparable damage
Flexible Power System	All batteries of the same voltage work with all tools in range
Durable	Less wear thanks to 13 mm, autolock full metal chuck
3 year tool warranty and 2 year battery warranty*	100% consumer confidence



You Tube youtube.com/BoschProfessionalUK

f facebook.com/BoschProfessionalPowerToolsUK



BOSCH
Invented for life

* Please register your tool, lithium-ion battery or charger online within four weeks of purchase to become eligible for the warranty services Bosch provide