



Free Height

TE Internal #: 1-5353906-0
PCB Mount Receptacle, Vertical, Board-to-Board, 280 Position, .6 mm [.024 in] Centerline, Gold (Au), Surface Mount, Signal, Natural, Reel, Free Height
[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Receptacle**
PCB Mount Orientation: **Vertical**
Connector System: **Board-to-Board**
Number of Positions: **280**
Centerline (Pitch): **.6 mm [.024 in]**

Features

Product Type Features

Ground Feature Type	Grounding Contact
PCB Connector Type	PCB Mount Receptacle
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Board-to-Board Configuration	Parallel
Stackable	Yes
PCB Mount Orientation	Vertical
Number of Positions	280

Electrical Characteristics

Operating Voltage	50 VAC
Insulation Resistance	2 MΩ
Dielectric Withstanding Voltage (Max)	200 VAC

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

PCB Contact Termination Area Plating Material Thickness	.05 μm, 1 μm[1.9685 μin][39.37 μin]
---	-------------------------------------



Contact Layout	Inline
Contact Mating Area Length	1 mm, 1.3 mm
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Gold, Tin
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Socket
Contact Current Rating (Max)	.5 A

Termination Features

Rectangular Termination Post & Tail Width	.9 mm[.035 in]
Rectangular Termination Post & Tail Thickness	.15 mm[.006 in]
Termination Method to PCB	Surface Mount

Mechanical Attachment

Mating Alignment Type	Polarized
PCB Mount Retention Type	Solder Peg
PCB Mount Alignment Type	Locating Posts
PCB Mount Retention	With
PCB Mount Alignment	With
Mating Alignment	With

Housing Features

Housing Material	High Temperature Thermoplastic
Centerline (Pitch)	.6 mm[.024 in]

Dimensions

Stack Height	4 mm, 6 mm, 8 mm, 12 mm[.472 in]
Connector Height	4 mm[.157 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Assembly Process Feature	Pick and Place Cover
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features



Packaging Quantity	650
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-5353232-0
[.6FHP06H,280,B,GIG,08/Sn,TR,NSYes](#)

TE Part # 1-5353185-0
[.6FHP06H,140,S,STD,08/Sn,TR,NSYes](#)

TE Part # 1-5353727-0
[.6FHP08H,280,B,GIG,08/Sn,ST,NSYes](#)

TE Part # 1-6123098-0
[.6FHP12H,280,B,GIG,08/Sn,HT,NS](#)



TE Part # 1-5353183-0
[.6FHP04H,140,S,STD,08/Sn,TR,NSYes](#)

TE Part # 6-5353284-0
[.6FHP04H,280,B,GIG,08/Sn,TR,SEYes](#)

TE Part # 1-5353187-0
[.6FHP08H,140,S,STD,08/Sn,TR,NSYes](#)

TE Part # 1-5316135-0
[.6FHP04H,140,S,STD,08/Sn,ST,NSYes](#)

TE Part # 1-5353233-0
[.6FHP08H,280,B,GIG,08/Sn,TR,NSYes](#)

Also in the Series | **Free Height**

Board-to-Board Headers & Receptacles(747)

PCB Headers & Receptacles(747)

Customers Also Bought

TE Part #1376137-1
[DYNAMIC D2100 HDR H ASSY 20P X](#)

TE Part #1-1827876-4
[DYNAMIC 1200D HDR ASSY H 8PX BLACK GOLD](#)

TE Part #179844-1
[AMP POWER D/LOCK T/HDR ASSY 2P](#)
[BLACK GOLD](#)

Documents

Product Drawings
[EMBOSS ASSY FH 0.6BTB REC. 4H 2ROW TYPE](#)

English

CAD Files
[3D PDF](#)

3D



Customer View Model

[ENG_CVM_CVM_1-5353906-0_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-5353906-0_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-5353906-0_A.3d_stp.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_1-5353906-0_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_1-5353906-0_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-5353906-0_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English